

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1191700

Luminaire Tested: **LDA4A25927D010TE LAR25NF 4LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1191700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26102)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A25927D010TE LAR25NF 4LLWW1
Description: PORTFOLIO 4" Lensed Wall Wash, Self-flanged, 25° Narrow Flood Optic,
at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1848.6 lumens
Efficiency: N/A
Efficacy: 59.8 lumens/watt
Spacing Criteria (0/90/45): 2.11 / 1.09 / 1.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1191700

CATALOG NUMBER: LDA4A25927D010TE LAR25NF 4LLWW1

Luminous Intensity Polar Plot



TEST NUMBER: P1191700

CATALOG NUMBER: LDA4A25927D010TE LAR25NF 4LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95
2	104	98	93	88	102	96	91	87	93	89	85		90	86	84		87
3	97	89	82	77	95	87	81	76	84	79	75		82	77	74		79
4	90	80	73	67	88	79	72	67	77	71	66		74	69	65		72
5	83	73	65	60	82	72	65	59	70	63	59		68	62	58		66
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		61
7	72	60	53	47	71	60	52	47	58	52	47		57	51	47		56
8	67	55	48	43	66	55	47	42	53	47	42		52	46	42		51
9	63	51	43	38	62	50	43	38	49	43	38		48	42	38		47
10	59	47	40	35	58	46	39	35	45	39	35		45	39	34		44

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63215	63215	63215
5°	105170	62713	39473
10°	170275	59969	26665
15°	251805	56838	20738
20°	342068	54644	24480
25°	411802	54861	33248
30°	448105	51416	31021
35°	434972	43306	24815
40°	376778	34860	20352
45°	293822	26863	17409
50°	194847	20091	13394
55°	108663	14752	8021
60°	57282	9794	3281
65°	30908	4932	350
70°	14750	1731	433
75°	5147	1144	572
80°	1705	1705	0
85°	5095	3397	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191700

CATALOG NUMBER: LDA4A25927D010TE LAR25NF 4LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.7	3.0
10°-20°	215.8	11.7
20°-30°	443.8	24.0
30°-40°	530.1	28.7
40°-50°	391.4	21.2
50°-60°	164.7	8.9
60°-70°	40.5	2.2
70°-80°	5.5	0.3
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	714.2	38.6
0°-40°	1244.3	67.3
0°-60°	1800.4	97.4
0°-90°	1848.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1848.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	512	512	512	512	512	
5°	849	732	506	363	319	97
15°	1972	1266	445	202	162	579
25°	3026	1607	403	243	244	1384
35°	2889	1436	288	172	165	1772
45°	1684	886	154	101	100	1293
55°	505	328	69	43	37	482
65°	106	72	17	4	1	115
75°	11	6	2	1	1	15
85°	4	4	2	1	0	3
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191700

CATALOG NUMBER: LDA4A25927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5
2.5°	666.5	658.1	658.1	660.5	667.7	661.7	656.9	652.1	656.9	646.0	649.6
5°	849.4	848.2	848.2	838.6	847.0	848.2	838.6	830.1	832.5	816.9	816.9
7.5°	1090.1	1082.8	1080.4	1067.2	1076.8	1075.6	1059.9	1045.5	1045.5	1020.3	1014.2
10°	1359.5	1349.9	1345.1	1328.2	1336.6	1331.8	1309.0	1287.3	1281.3	1245.2	1232.0
12.5°	1656.6	1650.7	1643.5	1621.8	1629.0	1619.4	1586.9	1555.6	1542.4	1494.2	1471.4
15°	1971.9	1981.6	1969.5	1944.2	1949.0	1932.2	1890.1	1846.8	1826.4	1761.4	1727.7
17.5°	2296.7	2308.8	2295.5	2266.7	2265.5	2242.6	2184.9	2131.9	2101.9	2018.8	1974.3
20°	2606.0	2609.6	2592.7	2561.4	2554.3	2522.9	2453.1	2378.6	2349.7	2247.4	2190.9
22.5°	2849.0	2862.2	2841.7	2818.9	2796.0	2756.4	2674.5	2592.7	2551.9	2435.1	2366.5
25°	3025.8	3056.0	3031.9	3005.4	2980.1	2933.2	2841.7	2753.9	2703.4	2573.5	2495.3
27.5°	3142.5	3171.5	3145.0	3114.9	3088.4	3034.3	2934.4	2850.2	2788.8	2646.9	2562.6
30°	3146.2	3181.0	3153.4	3120.8	3095.6	3041.5	2939.3	2852.6	2784.0	2642.1	2554.3
32.5°	3059.6	3087.2	3059.6	3031.9	3003.0	2951.2	2849.0	2766.0	2693.8	2557.9	2470.0
35°	2888.7	2912.7	2885.1	2852.6	2832.2	2786.4	2689.0	2609.6	2537.4	2412.2	2335.2
37.5°	2652.9	2674.5	2649.3	2631.2	2601.2	2560.2	2471.2	2400.2	2331.7	2218.6	2150.0
40°	2340.0	2385.8	2361.7	2349.7	2322.1	2287.1	2209.0	2146.4	2083.8	1985.2	1928.6
42.5°	2027.3	2070.6	2049.0	2040.5	2016.4	1986.4	1921.4	1868.5	1810.7	1728.9	1680.8
45°	1684.4	1730.1	1709.7	1706.1	1685.6	1662.7	1593.0	1565.2	1514.7	1437.7	1414.9
47.5°	1362.0	1370.4	1351.1	1352.3	1337.9	1322.2	1265.6	1248.9	1223.6	1164.6	1138.2
50°	1015.4	1021.5	1005.8	1010.6	1001.0	991.3	952.9	944.4	928.9	889.1	873.4
52.5°	699.1	726.7	715.8	720.7	715.8	712.2	696.6	682.2	675.0	649.6	642.5
55°	505.3	507.7	499.3	504.1	500.5	499.3	489.6	481.2	477.7	462.0	459.6
57.5°	350.1	352.5	352.5	350.1	348.9	346.5	340.5	335.7	333.3	329.6	322.4
60°	232.2	241.9	238.2	240.7	239.4	239.4	234.6	231.0	229.8	222.6	222.6
62.5°	158.8	164.8	162.4	163.6	162.4	162.4	158.8	156.4	156.4	155.2	151.6
65°	105.9	109.5	107.1	108.3	108.3	108.3	105.9	103.5	103.5	102.2	99.8
67.5°	67.4	69.8	68.6	69.8	68.6	69.8	67.4	66.2	65.0	65.0	63.8
70°	40.9	42.1	40.9	42.1	40.9	40.9	39.7	39.7	38.5	37.3	37.3
72.5°	21.7	22.9	22.9	22.9	22.9	22.9	21.7	20.5	20.5	20.5	19.3
75°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	9.6	9.6	9.6
77.5°	4.8	4.8	4.8	4.8	6.0	4.8	4.8	4.8	4.8	4.8	4.8
80°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
82.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
85°	3.6	3.6	3.6	3.6	3.6	3.6	4.8	4.8	4.8	4.8	3.6
87.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	6.0	6.0	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1191700

CATALOG NUMBER: LDA4A25927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5
2.5°	640.1	634.1	631.7	626.8	620.8	617.2	613.6	614.8	606.4	600.3	591.9
5°	801.3	788.0	780.8	770.0	756.8	746.0	736.3	731.5	715.8	705.0	682.2
7.5°	991.3	968.5	954.1	934.8	912.0	892.7	873.4	860.3	836.2	815.8	780.8
10°	1199.5	1164.6	1139.4	1110.5	1075.6	1044.3	1015.4	991.3	955.3	924.0	878.2
12.5°	1426.9	1377.5	1341.5	1299.4	1250.1	1206.8	1155.0	1127.3	1078.0	1034.7	975.8
15°	1668.7	1603.7	1553.2	1495.4	1430.6	1372.8	1306.6	1265.6	1200.8	1145.4	1072.0
17.5°	1900.9	1819.2	1753.0	1679.5	1599.0	1524.4	1446.1	1388.4	1309.0	1240.4	1152.5
20°	2103.1	2005.6	1925.0	1835.9	1740.9	1649.5	1564.0	1487.1	1394.4	1313.8	1213.9
22.5°	2267.9	2154.8	2062.1	1958.7	1849.2	1745.7	1648.3	1560.4	1454.6	1365.6	1256.1
25°	2387.0	2263.1	2159.6	2045.3	1925.0	1807.1	1703.7	1607.3	1491.8	1396.8	1280.1
27.5°	2449.5	2318.4	2209.0	2086.2	1958.7	1835.9	1724.0	1621.8	1500.3	1400.4	1280.1
30°	2438.8	2305.2	2192.1	2065.7	1937.1	1814.3	1697.6	1595.4	1470.2	1369.2	1248.9
32.5°	2355.7	2224.5	2113.8	1991.2	1864.9	1745.7	1629.0	1530.4	1405.2	1306.6	1189.9
35°	2218.6	2094.7	1990.0	1873.3	1754.2	1642.3	1536.4	1436.5	1316.3	1222.3	1112.9
37.5°	2040.5	1927.4	1832.3	1724.0	1614.6	1513.5	1408.9	1323.4	1216.3	1128.5	1021.5
40°	1827.5	1727.7	1643.5	1547.3	1448.5	1360.8	1272.9	1189.9	1085.2	1007.0	915.6
42.5°	1593.0	1507.5	1435.3	1351.1	1265.6	1191.1	1115.3	1043.1	956.5	885.5	800.1
45°	1340.3	1268.0	1209.2	1141.8	1070.8	1001.0	945.6	885.5	804.9	752.0	679.8
47.5°	1079.2	1023.9	979.4	927.7	871.0	827.7	774.8	726.7	667.7	618.4	559.4
50°	831.3	792.9	761.5	725.5	684.6	644.9	613.6	576.3	531.8	492.1	445.1
52.5°	614.8	589.6	570.3	546.2	518.6	498.1	469.3	441.5	407.9	377.8	341.7
55°	440.3	425.9	413.9	399.4	380.2	362.2	347.7	328.4	304.4	281.5	255.0
57.5°	316.4	300.8	299.6	283.9	276.7	263.5	250.3	235.8	219.0	203.3	184.1
60°	219.0	208.1	203.3	197.4	188.9	180.5	174.5	164.8	152.8	141.9	127.6
62.5°	147.9	140.7	138.4	136.0	128.8	125.1	117.9	111.9	103.5	95.0	85.5
65°	97.4	92.6	90.2	86.6	83.1	80.7	77.0	72.2	65.0	60.2	54.1
67.5°	61.4	57.8	55.3	54.1	50.5	49.3	45.7	43.3	38.5	36.1	32.4
70°	34.9	33.6	31.2	31.2	28.8	26.5	25.3	22.9	21.7	19.3	18.1
72.5°	18.1	18.1	16.9	15.7	14.5	14.5	13.3	12.1	10.8	9.6	9.6
75°	8.4	8.4	8.4	7.2	7.2	7.2	6.0	6.0	6.0	4.8	4.8
77.5°	4.8	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	2.4	2.4
80°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
82.5°	2.4	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
85°	3.6	2.4	2.4	2.4	2.4	3.6	3.6	3.6	3.6	3.6	3.6
87.5°	3.6	3.6	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191700

CATALOG NUMBER: LDA4A25927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5
2.5°	586.0	583.6	577.5	576.3	563.1	560.7	553.4	542.6	534.1	531.8	534.1
5°	673.7	662.9	644.9	641.3	619.6	612.4	596.7	579.9	565.5	557.0	553.4
7.5°	763.9	746.0	719.4	706.2	675.0	659.3	636.5	612.4	589.6	573.9	564.3
10°	850.6	821.7	773.6	762.7	724.3	699.1	667.7	635.3	606.4	584.8	569.1
12.5°	932.4	897.5	848.2	818.1	767.6	735.1	695.4	655.7	619.6	590.8	569.1
15°	1016.6	970.9	909.6	867.5	809.7	766.4	718.2	672.5	630.5	594.3	567.9
17.5°	1086.5	1029.9	957.7	907.2	839.8	788.0	732.7	679.8	634.1	593.1	563.1
20°	1138.2	1072.0	990.1	931.2	856.6	798.9	738.7	681.0	630.5	586.0	553.4
22.5°	1173.0	1097.2	1008.2	943.2	865.1	802.5	737.5	677.4	625.6	579.9	545.0
25°	1189.9	1108.0	1015.4	945.6	863.9	798.9	731.5	670.1	617.2	570.3	536.5
27.5°	1187.5	1100.8	1005.8	932.4	849.4	782.0	713.4	652.1	600.3	553.4	518.6
30°	1152.5	1067.2	970.9	896.3	814.6	747.2	678.6	618.4	567.9	519.8	487.2
32.5°	1098.4	1010.6	916.8	833.7	763.9	697.9	632.9	571.5	523.4	476.5	445.1
35°	1025.1	940.8	850.6	779.6	703.8	640.1	577.5	519.8	474.1	428.3	399.4
37.5°	939.6	859.1	776.0	702.7	636.5	577.5	518.6	466.8	421.0	380.2	352.5
40°	841.0	766.4	690.6	628.0	563.1	508.9	454.8	404.3	366.9	329.6	305.6
42.5°	733.9	667.7	599.1	545.0	486.0	437.9	386.2	350.1	314.0	280.3	261.0
45°	622.0	564.3	506.5	457.2	409.1	366.9	322.4	288.8	261.0	233.4	216.5
47.5°	511.3	462.0	415.1	375.3	333.3	298.4	267.1	237.0	210.5	187.7	174.5
50°	399.4	366.9	329.6	297.2	263.5	234.6	205.7	184.1	163.6	146.7	138.4
52.5°	311.6	281.5	251.5	225.0	200.9	176.9	157.6	139.6	125.1	114.3	108.3
55°	232.2	208.1	185.3	164.8	145.5	130.0	116.7	105.9	96.2	87.8	85.5
57.5°	166.0	147.9	132.4	116.7	104.7	95.0	86.6	79.4	73.4	67.4	66.2
60°	115.5	102.2	92.6	83.1	75.8	68.6	63.8	59.0	54.1	50.5	49.3
62.5°	77.0	69.8	62.6	57.8	54.1	48.1	45.7	42.1	39.7	36.1	34.9
65°	49.3	44.5	40.9	37.3	34.9	32.4	30.0	27.6	25.3	22.9	22.9
67.5°	30.0	26.5	25.3	22.9	20.5	19.3	18.1	15.7	14.5	14.5	13.3
70°	16.9	14.5	13.3	12.1	10.8	10.8	9.6	8.4	8.4	7.2	7.2
72.5°	8.4	8.4	7.2	7.2	6.0	6.0	4.8	4.8	4.8	3.6	3.6
75°	4.8	4.8	3.6	3.6	3.6	3.6	3.6	3.6	2.4	2.4	2.4
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
80°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
82.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
85°	3.6	3.6	3.6	3.6	2.4	2.4	2.4	2.4	2.4	2.4	2.4
87.5°	3.6	3.6	3.6	3.6	3.6	2.4	2.4	2.4	2.4	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191700

CATALOG NUMBER: LDA4A25927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	112.5°	135°	157.5°	180°
0°	512.5	512.5	512.5	512.5	512.5	512.5	512.5	512.5
2.5°	524.6	512.5	510.1	510.1	459.6	429.5	406.7	400.7
5°	536.5	519.8	511.3	506.5	416.3	363.4	328.4	318.8
7.5°	542.6	518.6	505.3	494.5	374.1	305.6	268.3	257.4
10°	540.2	511.3	493.3	478.8	335.7	261.0	222.6	212.9
12.5°	535.3	502.9	480.0	462.0	303.2	226.2	191.3	181.7
15°	530.6	493.3	466.8	445.1	276.7	202.1	170.8	162.4
17.5°	521.0	482.4	452.4	429.5	259.8	192.5	166.0	161.2
20°	510.1	470.5	439.1	416.3	255.0	202.1	186.5	186.5
22.5°	502.9	462.0	431.9	409.1	263.5	225.0	219.0	222.6
25°	493.3	454.8	424.7	403.1	271.9	243.1	239.4	244.3
27.5°	477.7	439.1	410.3	388.6	267.1	240.7	237.0	239.4
30°	446.4	409.1	383.8	361.0	247.9	222.6	216.5	217.8
32.5°	406.7	370.5	346.5	324.8	220.2	196.2	190.1	190.1
35°	363.4	329.6	306.8	287.6	193.7	172.1	166.0	164.8
37.5°	320.0	288.8	269.5	251.5	169.6	150.4	144.3	143.1
40°	276.7	249.1	231.0	216.5	149.2	133.6	127.6	126.4
42.5°	235.8	211.7	196.2	184.1	130.0	117.9	113.1	111.9
45°	195.0	175.7	163.6	154.0	113.1	101.0	99.8	99.8
47.5°	157.6	141.9	133.6	127.6	96.2	86.6	85.5	86.6
50°	126.4	115.5	109.5	104.7	81.9	73.4	69.8	69.8
52.5°	99.8	92.6	89.0	85.5	67.4	59.0	54.1	52.9
55°	79.4	73.4	71.0	68.6	52.9	43.3	38.5	37.3
57.5°	62.6	57.8	55.3	52.9	39.7	30.0	25.3	24.1
60°	46.9	43.3	40.9	39.7	27.6	18.1	14.5	13.3
62.5°	33.6	31.2	28.8	27.6	16.9	9.6	6.0	4.8
65°	20.5	20.5	18.1	16.9	8.4	3.6	2.4	1.2
67.5°	12.1	10.8	9.6	9.6	3.6	2.4	1.2	1.2
70°	6.0	6.0	4.8	4.8	2.4	1.2	1.2	1.2
72.5°	3.6	3.6	3.6	2.4	2.4	1.2	1.2	1.2
75°	2.4	2.4	2.4	2.4	2.4	1.2	1.2	1.2
77.5°	2.4	2.4	2.4	2.4	2.4	1.2	1.2	0.0
80°	2.4	2.4	2.4	2.4	2.4	1.2	1.2	0.0
82.5°	2.4	2.4	2.4	2.4	2.4	1.2	1.2	1.2
85°	2.4	2.4	2.4	2.4	2.4	1.2	1.2	0.0
87.5°	2.4	2.4	2.4	2.4	2.4	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)