

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1191880

Luminaire Tested: **LDA4A35927D010TE LAR25NF 4LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1191880
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26102)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A35927D010TE LAR25NF 4LLWW1
Description: PORTFOLIO 4" Lensed Wall Wash, Self-flanged, 25° Narrow Flood Optic,
at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2559.2 lumens
Efficiency: N/A
Efficacy: 54.3 lumens/watt
Spacing Criteria (0/90/45): 2.11 / 1.09 / 1.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1191880

CATALOG NUMBER: LDA4A35927D010TE LAR25NF 4LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191880

CATALOG NUMBER: LDA4A35927D010TE LAR25NF 4LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	102	109	106	103	101		102	100	98		98	96	95		95	93	92
2	104	98	93	88	102	96	91	87		93	89	85		90	86	84		87	84	82
3	97	89	82	77	95	87	81	76		84	79	75		82	77	74		79	76	73
4	90	80	73	67	88	79	72	67		77	71	66		74	69	65		72	68	65
5	83	73	65	60	82	72	65	59		70	63	59		68	62	58		66	61	58
6	78	66	58	53	76	65	58	53		64	57	52		62	56	52		61	55	52
7	72	60	53	47	71	60	52	47		58	52	47		57	51	47		56	50	46
8	67	55	48	43	66	55	47	42		53	47	42		52	46	42		51	46	42
9	63	51	43	38	62	50	43	38		49	43	38		48	42	38		47	42	38
10	59	47	40	35	58	46	39	35		45	39	35		45	39	34		44	38	34

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	87514	87514	87514
5°	145596	86820	54653
10°	235718	83027	36923
15°	348587	78687	28706
20°	473540	75646	33879
25°	570082	75942	46028
30°	620342	71171	42942
35°	602158	59945	34362
40°	521612	48257	28178
45°	406752	37190	24107
50°	269742	27824	18537
55°	150425	20408	11118
60°	79287	13568	4539
65°	42787	6830	496
70°	20448	2380	613
75°	7101	1573	810
80°	2344	2344	0
85°	7076	4670	0



TEST NUMBER: P1191880

CATALOG NUMBER: LDA4A35927D010TE LAR25NF 4LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.7	3.0
10°-20°	298.7	11.7
20°-30°	614.3	24.0
30°-40°	733.8	28.7
40°-50°	541.9	21.2
50°-60°	228.1	8.9
60°-70°	56.0	2.2
70°-80°	7.7	0.3
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	988.7	38.6
0°-40°	1722.5	67.3
0°-60°	2492.5	97.4
0°-90°	2559.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2559.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	710	710	710	710	710	
5°	1176	1013	701	503	441	134
15°	2730	1752	616	280	225	801
25°	4189	2225	558	336	338	1916
35°	3999	1989	398	238	228	2453
45°	2332	1226	213	140	138	1790
55°	700	455	95	60	52	667
65°	147	100	23	5	2	159
75°	15	8	3	2	2	21
85°	5	5	3	2	0	5
90°	0	0	0	0	0	

TEST NUMBER: P1191880

CATALOG NUMBER: LDA4A35927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5
2.5°	922.7	911.1	911.1	914.4	924.4	916.1	909.4	902.8	909.4	894.4	899.3
5°	1175.9	1174.2	1174.2	1160.9	1172.6	1174.2	1160.9	1149.2	1152.5	1131.0	1131.0
7.5°	1509.0	1499.0	1495.6	1477.4	1490.7	1489.0	1467.3	1447.4	1447.4	1412.5	1404.0
10°	1882.0	1868.8	1862.1	1838.8	1850.4	1843.7	1812.1	1782.1	1773.8	1723.8	1705.6
12.5°	2293.4	2285.1	2275.2	2245.2	2255.1	2241.9	2196.8	2153.6	2135.2	2068.6	2036.9
15°	2729.8	2743.2	2726.5	2691.5	2698.2	2674.8	2616.7	2556.7	2528.3	2438.4	2391.8
17.5°	3179.5	3196.2	3177.8	3137.9	3136.2	3104.6	3024.7	2951.3	2909.8	2794.8	2733.1
20°	3607.6	3612.6	3589.2	3546.0	3536.0	3492.6	3396.0	3292.8	3252.9	3111.2	3033.0
22.5°	3944.1	3962.3	3934.0	3902.4	3870.7	3815.9	3702.6	3589.2	3532.7	3371.0	3276.1
25°	4188.8	4230.6	4197.3	4160.5	4125.5	4060.6	3934.0	3812.4	3742.5	3562.7	3454.4
27.5°	4350.4	4390.5	4353.9	4312.1	4275.5	4200.6	4062.3	3945.8	3860.8	3664.3	3547.6
30°	4355.5	4403.7	4365.5	4320.4	4285.4	4210.5	4069.0	3949.1	3854.1	3657.6	3536.0
32.5°	4235.6	4273.8	4235.6	4197.3	4157.2	4085.6	3944.1	3829.1	3729.2	3541.0	3419.4
35°	3999.0	4032.3	3994.0	3949.1	3920.8	3857.5	3722.6	3612.6	3512.7	3339.4	3232.8
37.5°	3672.6	3702.6	3667.6	3642.6	3601.0	3544.3	3421.1	3322.8	3227.9	3071.3	2976.4
40°	3239.5	3302.8	3269.5	3252.9	3214.6	3166.2	3058.0	2971.4	2884.7	2748.2	2669.8
42.5°	2806.5	2866.5	2836.5	2824.8	2791.5	2749.9	2659.9	2586.7	2506.6	2393.5	2326.9
45°	2331.8	2395.1	2366.8	2361.8	2333.5	2301.9	2205.3	2166.8	2096.9	1990.4	1958.7
47.5°	1885.5	1897.1	1870.4	1872.1	1852.2	1830.5	1752.1	1728.9	1694.0	1612.3	1575.7
50°	1405.7	1414.1	1392.4	1399.0	1385.8	1372.4	1319.2	1307.4	1285.9	1230.9	1209.2
52.5°	967.8	1006.0	991.0	997.7	991.0	986.0	964.3	944.4	934.5	899.3	889.4
55°	699.5	702.8	691.2	697.9	692.9	691.2	677.8	666.2	661.2	639.5	636.2
57.5°	484.6	487.9	487.9	484.6	483.0	479.7	471.4	464.7	461.4	456.3	446.4
60°	321.4	334.8	329.7	333.2	331.4	331.4	324.7	319.8	318.1	308.2	308.2
62.5°	219.9	228.2	224.8	226.5	224.8	224.8	219.9	216.5	216.5	214.9	209.9
65°	146.6	151.6	148.3	149.9	149.9	149.9	146.6	143.3	143.3	141.5	138.2
67.5°	93.3	96.6	94.9	96.6	94.9	96.6	93.3	91.6	90.0	90.0	88.3
70°	56.7	58.3	56.7	58.3	56.7	56.7	55.0	55.0	53.3	51.7	51.7
72.5°	30.0	31.6	31.6	31.6	31.6	31.6	30.0	28.3	28.3	28.3	26.7
75°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	13.3	13.3	13.3
77.5°	6.6	6.6	6.6	6.6	8.3	6.6	6.6	6.6	6.6	6.6	6.6
80°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
82.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
85°	5.0	5.0	5.0	5.0	5.0	5.0	6.6	6.6	6.6	6.6	5.0
87.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	8.3	8.3	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1191880

CATALOG NUMBER: LDA4A35927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5
2.5°	886.1	877.8	874.5	867.7	859.4	854.4	849.5	851.1	839.5	831.1	819.5
5°	1109.3	1090.9	1080.9	1066.0	1047.6	1032.7	1019.3	1012.7	991.0	976.0	944.4
7.5°	1372.4	1340.7	1320.8	1294.2	1262.5	1235.8	1209.2	1190.9	1157.6	1129.3	1080.9
10°	1660.5	1612.3	1577.3	1537.4	1489.0	1445.8	1405.7	1372.4	1322.5	1279.1	1215.8
12.5°	1975.3	1907.0	1857.2	1798.8	1730.6	1670.6	1599.0	1560.6	1492.3	1432.3	1350.8
15°	2310.1	2220.2	2150.3	2070.2	1980.4	1900.4	1808.8	1752.1	1662.3	1585.6	1484.0
17.5°	2631.6	2518.4	2426.8	2325.1	2213.5	2110.3	2002.0	1922.1	1812.1	1717.2	1595.5
20°	2911.4	2776.5	2664.9	2541.6	2410.0	2283.5	2165.2	2058.6	1930.4	1818.7	1680.5
22.5°	3139.6	2983.0	2854.7	2711.6	2560.0	2416.7	2281.8	2160.2	2013.7	1890.5	1738.9
25°	3304.4	3132.9	2989.6	2831.4	2664.9	2501.7	2358.5	2225.1	2065.3	1933.7	1772.2
27.5°	3391.1	3209.5	3058.0	2888.1	2711.6	2541.6	2386.7	2245.2	2077.0	1938.7	1772.2
30°	3376.1	3191.2	3034.7	2859.7	2681.6	2511.6	2350.1	2208.6	2035.3	1895.4	1728.9
32.5°	3261.2	3079.6	2926.3	2756.5	2581.7	2416.7	2255.1	2118.6	1945.3	1808.8	1647.2
35°	3071.3	2899.8	2754.8	2593.3	2428.4	2273.5	2126.9	1988.7	1822.2	1692.1	1540.7
37.5°	2824.8	2668.2	2536.6	2386.7	2235.2	2095.2	1950.4	1832.1	1683.9	1562.2	1414.1
40°	2530.0	2391.8	2275.2	2142.0	2005.3	1883.8	1762.2	1647.2	1502.3	1394.1	1267.5
42.5°	2205.3	2087.0	1987.1	1870.4	1752.1	1648.9	1544.0	1444.1	1324.1	1225.9	1107.6
45°	1855.5	1755.4	1673.9	1580.6	1482.4	1385.8	1309.1	1225.9	1114.2	1041.0	941.1
47.5°	1494.0	1417.4	1355.8	1284.2	1205.9	1145.9	1072.6	1006.0	924.4	856.1	774.4
50°	1150.9	1097.7	1054.3	1004.4	947.7	892.7	849.5	797.8	736.1	681.3	616.2
52.5°	851.1	816.2	789.5	756.2	717.9	689.6	649.6	611.2	564.7	523.1	473.0
55°	609.6	589.7	572.9	552.9	526.4	501.4	481.3	454.6	421.3	389.7	353.1
57.5°	438.1	416.4	414.7	393.0	383.1	364.8	346.4	326.4	303.2	281.5	254.8
60°	303.2	288.1	281.5	273.2	261.5	249.9	241.6	228.2	211.6	196.5	176.6
62.5°	204.8	194.8	191.5	188.2	178.3	173.1	163.2	154.9	143.3	131.6	118.3
65°	134.9	128.2	124.9	120.0	115.0	111.7	106.5	99.9	90.0	83.3	74.9
67.5°	85.0	80.0	76.6	74.9	69.9	68.3	63.3	60.0	53.3	50.0	44.9
70°	48.4	46.6	43.2	43.2	39.9	36.6	35.0	31.6	30.0	26.7	25.0
72.5°	25.0	25.0	23.4	21.7	20.0	20.0	18.4	16.7	14.9	13.3	13.3
75°	11.6	11.6	11.6	9.9	9.9	9.9	8.3	8.3	8.3	6.6	6.6
77.5°	6.6	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	3.3	3.3
80°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
82.5°	3.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	5.0	3.3	3.3	3.3	3.3	5.0	5.0	5.0	5.0	5.0	5.0
87.5°	5.0	5.0	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191880

CATALOG NUMBER: LDA4A35927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5
2.5°	811.2	807.9	799.4	797.8	779.5	776.2	766.1	751.2	739.5	736.1	739.5
5°	932.6	917.7	892.7	887.7	857.8	847.8	826.1	802.7	782.9	771.1	766.1
7.5°	1057.6	1032.7	995.9	977.7	934.5	912.8	881.1	847.8	816.2	794.5	781.2
10°	1177.5	1137.6	1071.0	1055.9	1002.7	967.8	924.4	879.5	839.5	809.5	787.8
12.5°	1290.8	1242.5	1174.2	1132.6	1062.7	1017.6	962.6	907.8	857.8	817.8	787.8
15°	1407.3	1344.0	1259.2	1200.9	1120.9	1061.0	994.3	931.0	872.8	822.8	786.2
17.5°	1504.1	1425.7	1325.8	1255.9	1162.6	1090.9	1014.3	941.1	877.8	821.1	779.5
20°	1575.7	1484.0	1370.7	1289.2	1185.8	1105.9	1022.6	942.7	872.8	811.2	766.1
22.5°	1623.9	1519.0	1395.7	1305.8	1197.6	1110.9	1021.0	937.8	866.0	802.7	754.5
25°	1647.2	1533.9	1405.7	1309.1	1195.9	1105.9	1012.7	927.7	854.4	789.5	742.8
27.5°	1643.9	1524.0	1392.4	1290.8	1175.9	1082.6	987.6	902.8	831.1	766.1	717.9
30°	1595.5	1477.4	1344.0	1240.8	1127.6	1034.4	939.4	856.1	786.2	719.6	674.5
32.5°	1520.7	1399.0	1269.1	1154.2	1057.6	966.1	876.1	791.1	724.5	659.6	616.2
35°	1419.1	1302.4	1177.5	1079.3	974.4	886.1	799.4	719.6	656.3	593.0	552.9
37.5°	1300.8	1189.3	1074.3	972.7	881.1	799.4	717.9	646.2	582.9	526.4	487.9
40°	1164.3	1061.0	956.0	869.4	779.5	704.5	629.6	559.7	508.0	456.3	423.0
42.5°	1016.0	924.4	829.4	754.5	672.8	606.2	534.7	484.6	434.8	388.0	361.4
45°	861.1	781.2	701.2	632.9	566.3	508.0	446.4	399.8	361.4	323.1	299.7
47.5°	707.8	639.5	574.6	519.6	461.4	413.1	369.8	328.1	291.4	259.8	241.6
50°	552.9	508.0	456.3	411.4	364.8	324.7	284.8	254.8	226.5	203.1	191.5
52.5°	431.4	389.7	348.1	311.5	278.2	244.9	218.2	193.2	173.1	158.2	149.9
55°	321.4	288.1	256.5	228.2	201.5	179.9	161.5	146.6	133.2	121.6	118.3
57.5°	229.8	204.8	183.2	161.5	145.0	131.6	120.0	109.9	101.6	93.3	91.6
60°	159.9	141.5	128.2	115.0	104.9	94.9	88.3	81.7	74.9	69.9	68.3
62.5°	106.5	96.6	86.6	80.0	74.9	66.6	63.3	58.3	55.0	50.0	48.4
65°	68.3	61.6	56.7	51.7	48.4	44.9	41.6	38.3	35.0	31.6	31.6
67.5°	41.6	36.6	35.0	31.6	28.3	26.7	25.0	21.7	20.0	20.0	18.4
70°	23.4	20.0	18.4	16.7	14.9	14.9	13.3	11.6	11.6	9.9	9.9
72.5°	11.6	11.6	9.9	9.9	8.3	8.3	6.6	6.6	6.6	5.0	5.0
75°	6.6	6.6	5.0	5.0	5.0	5.0	5.0	5.0	3.3	3.3	3.3
77.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
80°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
82.5°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
85°	5.0	5.0	5.0	5.0	3.3	3.3	3.3	3.3	3.3	3.3	3.3
87.5°	5.0	5.0	5.0	5.0	5.0	3.3	3.3	3.3	3.3	3.3	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191880

CATALOG NUMBER: LDA4A35927D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	112.5°	135°	157.5°	180°
0°	709.5	709.5	709.5	709.5	709.5	709.5	709.5	709.5
2.5°	726.2	709.5	706.2	706.2	636.2	594.6	563.0	554.7
5°	742.8	719.6	707.8	701.2	576.3	503.0	454.6	441.4
7.5°	751.2	717.9	699.5	684.6	517.9	423.0	371.5	356.4
10°	747.9	707.8	682.9	662.9	464.7	361.4	308.2	294.8
12.5°	741.1	696.2	664.6	639.5	419.7	313.1	264.8	251.5
15°	734.5	682.9	646.2	616.2	383.1	279.8	236.4	224.8
17.5°	721.2	667.9	626.3	594.6	359.7	266.4	229.8	223.2
20°	706.2	651.3	607.9	576.3	353.1	279.8	258.1	258.1
22.5°	696.2	639.5	598.0	566.3	364.8	311.5	303.2	308.2
25°	682.9	629.6	588.0	558.0	376.4	336.5	331.4	338.2
27.5°	661.2	607.9	568.0	538.0	369.8	333.2	328.1	331.4
30°	618.0	566.3	531.3	499.7	343.1	308.2	299.7	301.5
32.5°	563.0	513.0	479.7	449.7	304.9	271.6	263.1	263.1
35°	503.0	456.3	424.7	398.1	268.1	238.2	229.8	228.2
37.5°	443.0	399.8	373.1	348.1	234.8	208.3	199.8	198.2
40°	383.1	344.8	319.8	299.7	206.6	184.9	176.6	175.0
42.5°	326.4	293.1	271.6	254.8	179.9	163.2	156.6	154.9
45°	269.9	243.2	226.5	213.2	156.6	139.8	138.2	138.2
47.5°	218.2	196.5	184.9	176.6	133.2	120.0	118.3	120.0
50°	175.0	159.9	151.6	145.0	113.3	101.6	96.6	96.6
52.5°	138.2	128.2	123.3	118.3	93.3	81.7	74.9	73.2
55°	109.9	101.6	98.3	94.9	73.2	60.0	53.3	51.7
57.5°	86.6	80.0	76.6	73.2	55.0	41.6	35.0	33.3
60°	64.9	60.0	56.7	55.0	38.3	25.0	20.0	18.4
62.5°	46.6	43.2	39.9	38.3	23.4	13.3	8.3	6.6
65°	28.3	28.3	25.0	23.4	11.6	5.0	3.3	1.7
67.5°	16.7	14.9	13.3	13.3	5.0	3.3	1.7	1.7
70°	8.3	8.3	6.6	6.6	3.3	1.7	1.7	1.7
72.5°	5.0	5.0	5.0	3.3	3.3	1.7	1.7	1.7
75°	3.3	3.3	3.3	3.3	3.3	1.7	1.7	1.7
77.5°	3.3	3.3	3.3	3.3	3.3	1.7	1.7	0.0
80°	3.3	3.3	3.3	3.3	3.3	1.7	1.7	0.0
82.5°	3.3	3.3	3.3	3.3	3.3	1.7	1.7	1.7
85°	3.3	3.3	3.3	3.3	3.3	1.7	1.7	0.0
87.5°	3.3	3.3	3.3	3.3	3.3	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)