

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1191898

Luminaire Tested: **LDA4A35930D010TE LAR25NF 4LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1191898
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26102)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A35930D010TE LAR25NF 4LLWW1
Description: PORTFOLIO 4" Lensed Wall Wash, Self-flanged, 25° Narrow Flood Optic,
at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2950.1 lumens
Efficiency: N/A
Efficacy: 62.6 lumens/watt
Spacing Criteria (0/90/45): 2.11 / 1.09 / 1.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1191898

CATALOG NUMBER: LDA4A35930D010TE LAR25NF 4LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191898

CATALOG NUMBER: LDA4A35930D010TE LAR25NF 4LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	89	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	80	73	67	88	79	72	67	77	71	66	74	69	65	72	68	65	63		
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56		
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	52	50		
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45		
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40		
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36		
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	100897	100897	100897
5°	167834	100081	62986
10°	271726	95715	42559
15°	401836	90716	33099
20°	545878	87197	39063
25°	657171	87537	53037
30°	715085	82038	49493
35°	694146	69100	39602
40°	601283	55631	32461
45°	468869	42877	27788
50°	310941	32046	21377
55°	173414	23526	12795
60°	91424	15616	5205
65°	49295	7822	584
70°	23550	2777	721
75°	8245	1811	953
80°	2699	2699	0
85°	8067	5378	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191898

CATALOG NUMBER: LDA4A35930D010TE LAR25NF 4LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.2	3.0
10°-20°	344.3	11.7
20°-30°	708.2	24.0
30°-40°	845.9	28.7
40°-50°	624.6	21.2
50°-60°	262.9	8.9
60°-70°	64.6	2.2
70°-80°	8.8	0.3
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1139.8	38.6
0°-40°	1985.6	67.3
0°-60°	2873.1	97.4
0°-90°	2950.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2950.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	818	818	818	818	818	
5°	1356	1167	808	580	509	155
15°	3147	2020	710	322	259	923
25°	4829	2565	643	388	390	2208
35°	4610	2292	459	275	263	2827
45°	2688	1413	246	161	159	2064
55°	806	524	109	69	60	769
65°	169	115	27	6	2	184
75°	17	10	4	2	2	25
85°	6	6	4	2	0	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191898

CATALOG NUMBER: LDA4A35930D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0
2.5°	1063.6	1050.2	1050.2	1054.1	1065.6	1055.9	1048.2	1040.7	1048.2	1031.0	1036.8
5°	1355.5	1353.5	1353.5	1338.2	1351.7	1353.5	1338.2	1324.8	1328.7	1303.7	1303.7
7.5°	1739.5	1728.0	1724.1	1703.0	1718.4	1716.4	1691.5	1668.5	1668.5	1628.1	1618.5
10°	2169.5	2154.2	2146.5	2119.7	2133.1	2125.4	2088.9	2054.4	2044.8	1987.2	1966.1
12.5°	2643.8	2634.1	2622.7	2588.2	2599.6	2584.3	2532.4	2482.5	2461.4	2384.6	2348.1
15°	3146.8	3162.2	3143.0	3102.6	3110.3	3083.5	3016.3	2947.1	2914.6	2810.9	2757.1
17.5°	3665.2	3684.5	3663.2	3617.3	3615.3	3578.8	3486.6	3402.2	3354.1	3221.7	3150.7
20°	4158.7	4164.4	4137.5	4087.6	4076.1	4026.1	3914.7	3795.8	3749.7	3586.5	3496.3
22.5°	4546.4	4567.5	4535.0	4498.5	4462.0	4398.6	4268.1	4137.5	4072.2	3885.9	3776.5
25°	4828.7	4876.8	4838.3	4796.0	4755.8	4680.9	4535.0	4394.8	4314.2	4106.9	3981.9
27.5°	5014.9	5061.1	5018.7	4970.8	4928.6	4842.1	4682.8	4548.4	4450.4	4224.0	4089.5
30°	5020.7	5076.4	5032.3	4980.4	4940.1	4853.7	4690.5	4552.2	4442.8	4216.3	4076.1
32.5°	4882.5	4926.6	4882.5	4838.3	4792.2	4709.6	4546.4	4414.0	4298.8	4081.8	3941.7
35°	4609.9	4648.2	4604.0	4552.2	4519.6	4446.7	4291.2	4164.4	4049.1	3849.5	3726.7
37.5°	4233.4	4268.1	4227.7	4198.9	4151.0	4085.6	3943.7	3830.3	3720.9	3540.4	3431.0
40°	3734.3	3807.3	3768.9	3749.7	3705.6	3649.8	3525.0	3425.3	3325.4	3167.9	3077.6
42.5°	3235.1	3304.3	3269.8	3256.2	3217.9	3169.8	3066.2	2981.6	2889.6	2759.1	2682.2
45°	2687.9	2760.9	2728.3	2722.4	2689.9	2653.4	2542.1	2497.9	2417.3	2294.3	2257.8
47.5°	2173.5	2186.9	2156.1	2158.1	2135.0	2110.0	2019.8	1992.9	1952.5	1858.5	1816.3
50°	1620.4	1630.1	1605.0	1612.7	1597.4	1582.0	1520.7	1507.2	1482.2	1418.8	1393.9
52.5°	1115.4	1159.6	1142.4	1150.1	1142.4	1136.7	1111.7	1088.6	1077.2	1036.8	1025.3
55°	806.4	810.3	796.7	804.4	798.7	796.7	781.5	767.9	762.2	737.2	733.4
57.5°	558.8	562.5	562.5	558.8	556.8	552.9	543.4	535.7	531.8	526.1	514.6
60°	370.6	385.9	380.2	384.0	382.0	382.0	374.3	368.6	366.6	355.2	355.2
62.5°	253.5	263.0	259.2	261.2	259.2	259.2	253.5	249.5	249.5	247.7	241.9
65°	168.9	174.7	170.9	172.8	172.8	172.8	168.9	165.2	165.2	163.2	159.3
67.5°	107.4	111.4	109.4	111.4	109.4	111.4	107.4	105.6	103.7	103.7	101.7
70°	65.3	67.2	65.3	67.2	65.3	65.3	63.3	63.3	61.5	59.5	59.5
72.5°	34.5	36.5	36.5	36.5	36.5	36.5	34.5	32.7	32.7	32.7	30.7
75°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	15.4	15.4	15.4
77.5°	7.7	7.7	7.7	7.7	9.6	7.7	7.7	7.7	7.7	7.7	7.7
80°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
82.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
85°	5.7	5.7	5.7	5.7	5.7	5.7	7.7	7.7	7.7	7.7	5.7
87.5°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	9.6	9.6	7.7	7.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191898

CATALOG NUMBER: LDA4A35930D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0
2.5°	1021.4	1011.8	1008.0	1000.3	990.7	984.9	979.2	981.2	967.6	958.1	944.5
5°	1278.6	1257.5	1246.1	1228.8	1207.7	1190.3	1175.0	1167.3	1142.4	1125.1	1088.6
7.5°	1582.0	1545.5	1522.5	1491.9	1455.4	1424.7	1393.9	1372.8	1334.4	1301.7	1246.1
10°	1914.3	1858.5	1818.3	1772.2	1716.4	1666.5	1620.4	1582.0	1524.4	1474.5	1401.6
12.5°	2277.1	2198.3	2140.8	2073.5	1994.9	1925.7	1843.1	1799.0	1720.3	1651.2	1557.1
15°	2662.9	2559.2	2478.6	2386.5	2282.9	2190.6	2085.0	2019.8	1916.1	1827.8	1710.7
17.5°	3033.5	2903.0	2797.3	2680.2	2551.7	2432.7	2307.7	2215.7	2088.9	1979.5	1839.4
20°	3356.1	3200.6	3071.9	2929.8	2778.2	2632.3	2495.9	2373.1	2225.3	2096.6	1937.2
22.5°	3619.1	3438.7	3290.9	3125.7	2951.0	2785.9	2630.4	2490.2	2321.3	2179.2	2004.4
25°	3809.2	3611.4	3446.4	3263.9	3071.9	2883.8	2718.7	2565.1	2380.8	2229.1	2042.8
27.5°	3909.0	3699.7	3525.0	3329.3	3125.7	2929.8	2751.4	2588.2	2394.2	2234.8	2042.8
30°	3891.8	3678.6	3498.2	3296.6	3091.2	2895.3	2709.0	2545.8	2346.2	2184.9	1992.9
32.5°	3759.2	3550.0	3373.4	3177.5	2975.9	2785.9	2599.6	2442.1	2242.5	2085.0	1898.9
35°	3540.4	3342.7	3175.6	2989.3	2799.3	2620.7	2451.8	2292.4	2100.4	1950.7	1775.9
37.5°	3256.2	3075.8	2924.1	2751.4	2576.6	2415.3	2248.2	2112.0	1941.1	1800.9	1630.1
40°	2916.4	2757.1	2622.7	2469.1	2311.6	2171.5	2031.4	1898.9	1731.8	1607.0	1461.1
42.5°	2542.1	2405.7	2290.5	2156.1	2019.8	1900.7	1779.8	1664.6	1526.4	1413.1	1276.8
45°	2138.8	2023.7	1929.5	1822.0	1708.7	1597.4	1509.0	1413.1	1284.5	1200.0	1084.8
47.5°	1722.1	1633.8	1562.8	1480.3	1390.0	1321.0	1236.4	1159.6	1065.6	986.9	892.7
50°	1326.7	1265.2	1215.3	1157.8	1092.5	1029.1	979.2	919.7	848.6	785.3	710.4
52.5°	981.2	940.8	910.0	871.6	827.5	794.9	748.8	704.6	650.8	602.9	545.2
55°	702.7	679.6	660.5	637.4	606.7	577.9	554.9	524.1	485.7	449.2	407.0
57.5°	505.0	480.0	478.0	453.1	441.5	420.4	399.3	376.3	349.5	324.4	293.7
60°	349.5	332.1	324.4	314.8	301.4	288.0	278.3	263.0	243.8	226.5	203.6
62.5°	236.1	224.7	220.8	217.0	205.4	199.7	188.2	178.6	165.2	151.7	136.4
65°	155.5	147.8	144.1	138.2	132.5	128.7	122.8	115.1	103.7	96.0	86.3
67.5°	98.0	92.2	88.3	86.3	80.6	78.7	72.9	69.2	61.5	57.6	51.8
70°	55.6	53.8	49.9	49.9	46.1	42.2	40.4	36.5	34.5	30.7	28.8
72.5°	28.8	28.8	26.8	25.0	23.1	23.1	21.1	19.1	17.3	15.4	15.4
75°	13.4	13.4	13.4	11.5	11.5	11.5	9.6	9.6	9.6	7.7	7.7
77.5°	7.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	3.8	3.8
80°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
82.5°	3.8	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
85°	5.7	3.8	3.8	3.8	3.8	5.7	5.7	5.7	5.7	5.7	5.7
87.5°	5.7	5.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1191898

CATALOG NUMBER: LDA4A35930D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0
2.5°	935.1	931.1	921.6	919.7	898.6	894.7	883.2	865.9	852.5	848.6	852.5
5°	1075.2	1057.9	1029.1	1023.4	988.9	977.3	952.2	925.4	902.4	888.9	883.2
7.5°	1219.1	1190.3	1148.1	1127.0	1077.2	1052.1	1015.7	977.3	940.8	915.8	900.4
10°	1357.5	1311.3	1234.5	1217.3	1155.8	1115.4	1065.6	1013.7	967.6	933.1	908.1
12.5°	1488.0	1432.3	1353.5	1305.6	1225.0	1173.2	1109.7	1046.4	988.9	942.7	908.1
15°	1622.4	1549.4	1451.5	1384.3	1292.2	1223.0	1146.2	1073.2	1006.0	948.5	906.3
17.5°	1733.7	1643.5	1528.3	1447.7	1340.1	1257.5	1169.2	1084.8	1011.8	946.5	898.6
20°	1816.3	1710.7	1580.2	1486.0	1366.9	1274.9	1178.9	1086.7	1006.0	935.1	883.2
22.5°	1871.9	1751.1	1609.0	1505.3	1380.5	1280.6	1176.9	1080.9	998.3	925.4	869.8
25°	1898.9	1768.2	1620.4	1509.0	1378.5	1274.9	1167.3	1069.5	984.9	910.0	856.2
27.5°	1895.0	1756.8	1605.0	1488.0	1355.5	1248.0	1138.5	1040.7	958.1	883.2	827.5
30°	1839.4	1703.0	1549.4	1430.4	1299.9	1192.3	1082.9	986.9	906.3	829.4	777.6
32.5°	1752.9	1612.7	1462.9	1330.5	1219.1	1113.6	1010.0	912.0	835.1	760.3	710.4
35°	1635.8	1501.4	1357.5	1244.1	1123.1	1021.4	921.6	829.4	756.5	683.5	637.4
37.5°	1499.6	1370.9	1238.4	1121.3	1015.7	921.6	827.5	744.9	671.9	606.7	562.5
40°	1342.1	1223.0	1102.0	1002.3	898.6	812.1	725.7	645.1	585.6	526.1	487.6
42.5°	1171.2	1065.6	956.2	869.8	775.6	698.9	616.3	558.8	501.1	447.4	416.7
45°	992.6	900.4	808.3	729.5	652.8	585.6	514.6	460.8	416.7	372.5	345.5
47.5°	816.0	737.2	662.5	599.0	531.8	476.2	426.2	378.2	336.0	299.6	278.3
50°	637.4	585.6	526.1	474.2	420.4	374.3	328.4	293.7	261.2	234.2	220.8
52.5°	497.3	449.2	401.3	359.1	320.7	282.2	251.5	222.7	199.7	182.3	172.8
55°	370.6	332.1	295.7	263.0	232.4	207.4	186.3	168.9	153.6	140.1	136.4
57.5°	264.9	236.1	211.1	186.3	167.0	151.7	138.2	126.7	117.1	107.4	105.6
60°	184.3	163.2	147.8	132.5	121.0	109.4	101.7	94.0	86.3	80.6	78.7
62.5°	122.8	111.4	99.9	92.2	86.3	76.9	72.9	67.2	63.3	57.6	55.6
65°	78.7	71.0	65.3	59.5	55.6	51.8	48.1	44.2	40.4	36.5	36.5
67.5°	48.1	42.2	40.4	36.5	32.7	30.7	28.8	25.0	23.1	23.1	21.1
70°	26.8	23.1	21.1	19.1	17.3	17.3	15.4	13.4	13.4	11.5	11.5
72.5°	13.4	13.4	11.5	11.5	9.6	9.6	7.7	7.7	7.7	5.7	5.7
75°	7.7	7.7	5.7	5.7	5.7	5.7	5.7	5.7	3.8	3.8	3.8
77.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
80°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
82.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
85°	5.7	5.7	5.7	5.7	3.8	3.8	3.8	3.8	3.8	3.8	3.8
87.5°	5.7	5.7	5.7	5.7	5.7	3.8	3.8	3.8	3.8	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1191898

CATALOG NUMBER: LDA4A35930D010TE LAR25NF 4LLWW1

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	112.5°	135°	157.5°	180°
0°	818.0	818.0	818.0	818.0	818.0	818.0	818.0	818.0
2.5°	837.1	818.0	814.0	814.0	733.4	685.4	648.9	639.4
5°	856.2	829.4	816.0	808.3	664.3	579.9	524.1	508.7
7.5°	865.9	827.5	806.4	789.0	597.0	487.6	428.1	410.9
10°	862.1	816.0	787.2	764.2	535.7	416.7	355.2	339.8
12.5°	854.4	802.6	766.1	737.2	483.9	360.9	305.3	289.9
15°	846.7	787.2	744.9	710.4	441.5	322.5	272.6	259.2
17.5°	831.4	769.9	722.0	685.4	414.7	307.3	264.9	257.2
20°	814.0	750.8	700.7	664.3	407.0	322.5	297.6	297.6
22.5°	802.6	737.2	689.3	652.8	420.4	359.1	349.5	355.2
25°	787.2	725.7	677.7	643.2	433.8	387.9	382.0	389.7
27.5°	762.2	700.7	654.8	620.1	426.2	384.0	378.2	382.0
30°	712.3	652.8	612.4	576.0	395.6	355.2	345.5	347.5
32.5°	648.9	591.3	552.9	518.4	351.4	313.0	303.3	303.3
35°	579.9	526.1	489.6	458.9	309.1	274.6	264.9	263.0
37.5°	510.7	460.8	430.1	401.3	270.6	240.1	230.4	228.5
40°	441.5	397.4	368.6	345.5	238.1	213.1	203.6	201.6
42.5°	376.3	337.9	313.0	293.7	207.4	188.2	180.5	178.6
45°	311.0	280.3	261.2	245.8	180.5	161.2	159.3	159.3
47.5°	251.5	226.5	213.1	203.6	153.6	138.2	136.4	138.2
50°	201.6	184.3	174.7	167.0	130.5	117.1	111.4	111.4
52.5°	159.3	147.8	142.1	136.4	107.4	94.0	86.3	84.5
55°	126.7	117.1	113.3	109.4	84.5	69.2	61.5	59.5
57.5°	99.9	92.2	88.3	84.5	63.3	48.1	40.4	38.4
60°	74.9	69.2	65.3	63.3	44.2	28.8	23.1	21.1
62.5°	53.8	49.9	46.1	44.2	26.8	15.4	9.6	7.7
65°	32.7	32.7	28.8	26.8	13.4	5.7	3.8	2.0
67.5°	19.1	17.3	15.4	15.4	5.7	3.8	2.0	2.0
70°	9.6	9.6	7.7	7.7	3.8	2.0	2.0	2.0
72.5°	5.7	5.7	5.7	3.8	3.8	2.0	2.0	2.0
75°	3.8	3.8	3.8	3.8	3.8	2.0	2.0	2.0
77.5°	3.8	3.8	3.8	3.8	3.8	2.0	2.0	0.0
80°	3.8	3.8	3.8	3.8	3.8	2.0	2.0	0.0
82.5°	3.8	3.8	3.8	3.8	3.8	2.0	2.0	2.0
85°	3.8	3.8	3.8	3.8	3.8	2.0	2.0	0.0
87.5°	3.8	3.8	3.8	3.8	3.8	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)