

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210733

Luminaire Tested: **LE_4B10D010 EC4B10208027 4LBS1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210733
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208027 4LBS1H
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1170.2 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210733

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBS1H

Luminous Intensity Polar Plot






TEST NUMBER: P210733

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	111	107	104	101	108	105	102	99		101	98	96			97	95	93			93
2	102	96	90	85	100	94	88	84		90	86	82			87	83	80			84
3	95	85	78	73	92	84	77	72		81	75	71			78	74	70			76
4	87	77	69	63	85	75	68	63		73	67	62			71	65	61			69
5	81	69	61	55	79	68	61	55		66	60	55			64	59	54			63
6	75	63	55	49	73	62	54	49		60	54	49			59	53	48			57
7	70	58	50	44	68	57	49	44		55	49	44			54	48	43			53
8	65	53	45	40	64	52	45	40		51	44	39			50	44	39			49
9	61	49	41	36	60	48	41	36		47	40	36			46	40	36			45
10	58	45	38	33	56	45	38	33		44	37	33			43	37	33			42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210733

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.3	4.9
10°-20°	155.8	13.3
20°-30°	216.4	18.5
30°-40°	236.1	20.2
40°-50°	220.3	18.8
50°-60°	167.2	14.3
60°-70°	91.5	7.8
70°-80°	25.2	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	429.5	36.7
0°-40°	665.6	56.9
0°-60°	1053.1	90.0
0°-90°	1170.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1170.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	612	
5°	607	57
15°	555	156
25°	470	216
35°	378	236
45°	286	220
55°	187	167
65°	92	92
75°	22	25
85°	0	0
90°	0	



TEST NUMBER: P210733

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	612.0
2.5°	612.0
5°	606.8
7.5°	599.1
10°	587.5
12.5°	572.0
15°	555.3
17.5°	534.6
20°	515.4
22.5°	492.2
25°	470.3
27.5°	448.3
30°	423.9
32.5°	400.7
35°	377.5
37.5°	354.3
40°	332.5
42.5°	309.3
45°	286.1
47.5°	262.9
50°	237.1
52.5°	212.6
55°	186.8
57.5°	162.3
60°	137.8
62.5°	113.3
65°	91.5
67.5°	70.9
70°	52.8
72.5°	36.1
75°	21.9
77.5°	10.3
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)