

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210737

Luminaire Tested: **LE\_4B10D010 EC4B10208027 4LBS1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P210737  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B10D010 EC4B10208027 4LBS1WMH  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1186.4 lumens  
Efficiency: N/A  
Efficacy: 119.8 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210737

CATALOG NUMBER: LE\_4B10D010 EC4B10208027 4LBS1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P210737

CATALOG NUMBER: LE\_4B10D010 EC4B10208027 4LBS1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |  |  |  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0 |  |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |  |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |  |  |  |
| 1   | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 102 | 100 | 97  | 98  | 96  | 94  | 95  | 93  | 92  | 90  |    |    |   |  |  |  |
| 2   | 104 | 98  | 92  | 88  | 102 | 96  | 91  | 87  | 92  | 88  | 85  | 89  | 86  | 83  | 86  | 84  | 81  | 79  |    |    |   |  |  |  |
| 3   | 96  | 88  | 82  | 76  | 94  | 87  | 81  | 76  | 84  | 79  | 74  | 81  | 77  | 73  | 79  | 75  | 72  | 70  |    |    |   |  |  |  |
| 4   | 90  | 80  | 73  | 67  | 88  | 79  | 72  | 67  | 76  | 70  | 66  | 74  | 69  | 65  | 72  | 68  | 64  | 62  |    |    |   |  |  |  |
| 5   | 83  | 73  | 65  | 59  | 82  | 72  | 64  | 59  | 70  | 63  | 59  | 68  | 62  | 58  | 66  | 61  | 57  | 56  |    |    |   |  |  |  |
| 6   | 78  | 66  | 59  | 53  | 76  | 65  | 58  | 53  | 64  | 57  | 53  | 62  | 57  | 52  | 61  | 56  | 52  | 50  |    |    |   |  |  |  |
| 7   | 73  | 61  | 53  | 48  | 71  | 60  | 53  | 48  | 59  | 52  | 48  | 57  | 52  | 47  | 56  | 51  | 47  | 45  |    |    |   |  |  |  |
| 8   | 68  | 56  | 49  | 44  | 67  | 56  | 48  | 43  | 54  | 48  | 43  | 53  | 47  | 43  | 52  | 47  | 43  | 41  |    |    |   |  |  |  |
| 9   | 64  | 52  | 45  | 40  | 63  | 52  | 45  | 40  | 50  | 44  | 40  | 49  | 44  | 39  | 49  | 43  | 39  | 38  |    |    |   |  |  |  |
| 10  | 60  | 48  | 41  | 37  | 59  | 48  | 41  | 37  | 47  | 41  | 36  | 46  | 40  | 36  | 45  | 40  | 36  | 35  |    |    |   |  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P210737

CATALOG NUMBER: LE\_4B10D010 EC4B10208027 4LBS1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 69.5   | 5.9       |
| 10°-20°   | 184.2  | 15.5      |
| 20°-30°   | 247.3  | 20.8      |
| 30°-40°   | 253.2  | 21.3      |
| 40°-50°   | 219.2  | 18.5      |
| 50°-60°   | 145.8  | 12.3      |
| 60°-70°   | 59.8   | 5.0       |
| 70°-80°   | 7.1    | 0.6       |
| 80°-90°   | 0.3    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 501.0  | 42.2      |
| 0°-40°    | 754.2  | 63.6      |
| 0°-60°    | 1119.1 | 94.3      |
| 0°-90°    | 1186.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1186.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 752 |      |
| 5°  | 740 | 69   |
| 15° | 658 | 184  |
| 25° | 540 | 247  |
| 35° | 404 | 253  |
| 45° | 285 | 219  |
| 55° | 162 | 146  |
| 65° | 59  | 60   |
| 75° | 3   | 7    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P210737

CATALOG NUMBER: LE\_4B10D010 EC4B10208027 4LBS1WMH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 751.9 |
| 2.5°  | 750.4 |
| 5°    | 740.2 |
| 7.5°  | 724.7 |
| 10°   | 703.7 |
| 12.5° | 680.3 |
| 15°   | 657.8 |
| 17.5° | 629.1 |
| 20°   | 601.1 |
| 22.5° | 571.5 |
| 25°   | 539.6 |
| 27.5° | 505.4 |
| 30°   | 471.2 |
| 32.5° | 437.0 |
| 35°   | 404.4 |
| 37.5° | 373.3 |
| 40°   | 343.7 |
| 42.5° | 314.1 |
| 45°   | 285.4 |
| 47.5° | 255.1 |
| 50°   | 224.0 |
| 52.5° | 192.8 |
| 55°   | 161.7 |
| 57.5° | 134.6 |
| 60°   | 106.5 |
| 62.5° | 80.9  |
| 65°   | 59.0  |
| 67.5° | 38.9  |
| 70°   | 22.5  |
| 72.5° | 10.9  |
| 75°   | 3.1   |
| 77.5° | 1.5   |
| 80°   | 0.8   |
| 82.5° | 0.8   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)