

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210788

Luminaire Tested: **LE_4B10D010 EC4B10209727 4LBPS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209727 4LBPS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 948.3 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210788

CATALOG NUMBER: LE_4B10D010 EC4B10209727 4LBPS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P210788

CATALOG NUMBER: LE_4B10D010 EC4B10209727 4LBPS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210788

CATALOG NUMBER: LE_4B10D010 EC4B10209727 4LBPS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.2	3.8
10°-20°	103.2	10.9
20°-30°	155.4	16.4
30°-40°	184.9	19.5
40°-50°	184.6	19.5
50°-60°	150.1	15.8
60°-70°	92.4	9.7
70°-80°	35.8	3.8
80°-90°	5.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	294.8	31.1
0°-40°	479.7	50.6
0°-60°	814.5	85.9
0°-90°	948.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	948.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	382	
5°	381	36
15°	366	103
25°	338	155
35°	296	185
45°	240	185
55°	168	150
65°	93	92
75°	33	36
85°	4	6
90°	0	



TEST NUMBER: P210788

CATALOG NUMBER: LE_4B10D010 EC4B10209727 4LBPS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	382.1
2.5°	382.7
5°	380.9
7.5°	378.7
10°	375.8
12.5°	370.9
15°	366.3
17.5°	359.6
20°	352.3
22.5°	345.6
25°	338.3
27.5°	328.2
30°	318.0
32.5°	308.4
35°	296.1
37.5°	282.6
40°	270.3
42.5°	255.1
45°	239.9
47.5°	223.6
50°	206.2
52.5°	188.3
55°	168.0
57.5°	148.4
60°	129.2
62.5°	110.7
65°	92.7
67.5°	75.9
70°	60.1
72.5°	45.5
75°	32.6
77.5°	21.3
80°	12.9
82.5°	7.9
85°	4.5
87.5°	2.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)