

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210740

Luminaire Tested: **LE_4B10D010 EC4B10208027 4LB1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210740
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208027 4LB1WH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 996.0 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210740

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LB1WH

Luminous Intensity Polar Plot






TEST NUMBER: P210740

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LB1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	67	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210740

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LB1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.1	6.1
10°-20°	176.2	17.7
20°-30°	260.0	26.1
30°-40°	256.5	25.8
40°-50°	157.0	15.8
50°-60°	60.2	6.0
60°-70°	18.8	1.9
70°-80°	5.5	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	497.3	49.9
0°-40°	753.8	75.7
0°-60°	970.9	97.5
0°-90°	996.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	996.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	642	
5°	642	61
15°	624	176
25°	569	260
35°	416	257
45°	201	157
55°	64	60
65°	18	19
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P210740

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LB1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	641.9
2.5°	643.3
5°	641.9
7.5°	640.6
10°	636.6
12.5°	631.2
15°	624.4
17.5°	616.3
20°	604.1
22.5°	590.6
25°	569.0
27.5°	542.0
30°	508.2
32.5°	466.3
35°	416.2
37.5°	360.9
40°	304.0
42.5°	251.4
45°	201.4
47.5°	156.7
50°	118.9
52.5°	87.8
55°	63.6
57.5°	44.5
60°	32.5
62.5°	24.4
65°	17.5
67.5°	13.6
70°	9.5
72.5°	6.7
75°	5.5
77.5°	2.7
80°	2.7
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)