

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210818

Luminaire Tested: **LE_4B10D010 EC4B10208030 4LBS1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208030 4LBS1B
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1075.2 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210818

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P210818

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100	108	105	101	98		100	98	95		97	94	93		93	91	90
2	102	95	89	84	100	93	88	83		90	85	81		86	83	79		84	80	78
3	94	84	77	72	91	83	76	71		80	74	70		77	73	69		75	71	67
4	86	76	68	62	84	74	67	61		72	65	60		70	64	60		68	63	59
5	80	68	60	54	78	67	59	53		65	58	53		63	57	52		61	56	52
6	74	62	53	47	72	61	53	47		59	52	47		57	51	46		56	50	46
7	69	56	48	42	67	55	48	42		54	47	42		52	46	41		51	45	41
8	64	51	43	38	63	51	43	38		49	42	37		48	42	37		47	41	37
9	60	47	39	34	59	47	39	34		46	39	34		45	38	34		44	38	34
10	56	44	36	31	55	43	36	31		42	36	31		41	35	31		40	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210818

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.8	4.2
10°-20°	127.0	11.8
20°-30°	189.0	17.6
30°-40°	219.9	20.5
40°-50°	214.3	19.9
50°-60°	164.8	15.3
60°-70°	91.1	8.5
70°-80°	24.1	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.7	33.6
0°-40°	580.6	54.0
0°-60°	959.8	89.3
0°-90°	1075.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1075.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	474	
5°	472	45
15°	450	127
25°	410	189
35°	353	220
45°	278	214
55°	184	165
65°	91	91
75°	20	24
85°	0	0
90°	0	



TEST NUMBER: P210818

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	474.3
2.5°	474.3
5°	471.5
7.5°	467.5
10°	464.8
12.5°	456.6
15°	449.7
17.5°	443.0
20°	433.4
22.5°	423.9
25°	410.3
27.5°	396.6
30°	383.0
32.5°	368.0
35°	353.0
37.5°	334.0
40°	317.6
42.5°	299.9
45°	278.1
47.5°	257.6
50°	234.4
52.5°	209.8
55°	184.0
57.5°	159.5
60°	136.3
62.5°	113.1
65°	91.3
67.5°	70.9
70°	51.7
72.5°	35.4
75°	20.4
77.5°	9.5
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)