

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210741

Luminaire Tested: **LE_4B10D010 EC4B10208027 4LBW1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210741
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208027 4LBW1LI
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1179.8 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210741

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBW1LI

Luminous Intensity Polar Plot





TEST NUMBER: P210741

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBW1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210741

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBW1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.7	6.0
10°-20°	223.1	18.9
20°-30°	348.0	29.5
30°-40°	338.6	28.7
40°-50°	169.1	14.3
50°-60°	26.2	2.2
60°-70°	3.2	0.3
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	641.8	54.4
0°-40°	980.4	83.1
0°-60°	1175.7	99.7
0°-90°	1179.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1179.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	723	
5°	732	71
15°	788	223
25°	765	348
35°	550	339
45°	212	169
55°	22	26
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P210741

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBW1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	722.9
2.5°	725.6
5°	732.3
7.5°	743.1
10°	756.7
12.5°	774.2
15°	787.8
17.5°	798.5
20°	799.9
22.5°	790.4
25°	764.8
27.5°	727.0
30°	679.6
32.5°	620.1
35°	550.0
37.5°	472.9
40°	391.8
42.5°	305.3
45°	212.2
47.5°	136.4
50°	82.5
52.5°	44.5
55°	21.6
57.5°	9.5
60°	5.5
62.5°	4.1
65°	2.7
67.5°	2.7
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)