

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210745

Luminaire Tested: **LE_4B10D010 EC4B10209027 4LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209027 4LBCS1MMS
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 901.7 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210745

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBCS1MMS

Luminous Intensity Polar Plot






TEST NUMBER: P210745

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88		
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76		
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65		
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50		
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44		
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40		
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36		
9	60	48	40	34	59	47	40	34	46	39	34	45	39	34	44	38	34	32		
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210745

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.0	4.3
10°-20°	109.5	12.1
20°-30°	159.9	17.7
30°-40°	182.9	20.3
40°-50°	175.8	19.5
50°-60°	135.7	15.1
60°-70°	75.8	8.4
70°-80°	22.1	2.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	308.4	34.2
0°-40°	491.4	54.5
0°-60°	802.9	89.0
0°-90°	901.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	901.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	414	
5°	410	39
15°	388	109
25°	348	160
35°	293	183
45°	229	176
55°	152	136
65°	76	76
75°	19	22
85°	1	1
90°	0	



TEST NUMBER: P210745

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	414.1
2.5°	414.1
5°	410.5
7.5°	408.8
10°	403.0
12.5°	396.0
15°	388.4
17.5°	380.8
20°	369.8
22.5°	361.0
25°	347.5
27.5°	334.2
30°	320.7
32.5°	307.4
35°	292.8
37.5°	278.2
40°	261.2
42.5°	246.2
45°	229.2
47.5°	210.0
50°	191.9
52.5°	172.0
55°	152.2
57.5°	131.8
60°	112.5
62.5°	93.3
65°	75.9
67.5°	59.5
70°	44.3
72.5°	30.9
75°	19.3
77.5°	9.9
80°	3.5
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)