

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210752

Luminaire Tested: **LE_4B10D010 EC4B10209027 4LBM1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210752
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35174)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209027 4LBM1WH
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 785.3 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210752

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBM1WH

Luminous Intensity Polar Plot





TEST NUMBER: P210752

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBM1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	105	105	103	101		101	100	98		98
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101897
5°	100641
10°	96778
15°	89745
20°	80658
25°	69223
30°	53859
35°	34813
40°	18528
45°	7710
50°	2567
55°	1105
60°	765
65°	595
70°	383
75°	507
80°	0
85°	0



TEST NUMBER: P210752

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBM1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	11.0
10°-20°	221.5	28.2
20°-30°	259.9	33.1
30°-40°	164.5	20.9
40°-50°	44.0	5.6
50°-60°	6.2	0.8
60°-70°	2.3	0.3
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	567.6	72.3
0°-40°	732.0	93.2
0°-60°	782.2	99.6
0°-90°	785.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	785.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	933	
5°	918	86
15°	793	222
25°	574	260
35°	261	164
45°	50	44
55°	6	6
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P210752

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBM1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	932.6
2.5°	929.2
5°	917.6
7.5°	899.0
10°	872.3
12.5°	837.5
15°	793.4
17.5°	748.2
20°	693.7
22.5°	638.0
25°	574.2
27.5°	504.6
30°	426.9
32.5°	342.2
35°	261.0
37.5°	189.1
40°	129.9
42.5°	83.5
45°	49.9
47.5°	27.8
50°	15.1
52.5°	8.1
55°	5.8
57.5°	4.6
60°	3.5
62.5°	3.5
65°	2.3
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)