

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211158

Luminaire Tested: **LE_4B15D010 EC4B10209727 4LBM1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211158
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209727 4LBM1WH
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 951.1 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211158

CATALOG NUMBER: LE_4B15D010 EC4B10209727 4LBM1WH

Luminous Intensity Polar Plot





TEST NUMBER: P211158

CATALOG NUMBER: LE_4B15D010 EC4B10209727 4LBM1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94																												
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																												
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81																												
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																												
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																												
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66																												
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62																												
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58																												
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55																												
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211158

CATALOG NUMBER: LE_4B15D010 EC4B10209727 4LBM1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.3	11.0
10°-20°	268.3	28.2
20°-30°	314.7	33.1
30°-40°	199.2	20.9
40°-50°	53.4	5.6
50°-60°	7.5	0.8
60°-70°	2.8	0.3
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.3	72.3
0°-40°	886.5	93.2
0°-60°	947.4	99.6
0°-90°	951.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	951.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1130	
5°	1111	104
15°	961	268
25°	695	315
35°	316	199
45°	60	53
55°	7	7
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P211158

CATALOG NUMBER: LE_4B15D010 EC4B10209727 4LBM1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1129.5
2.5°	1125.2
5°	1111.2
7.5°	1088.8
10°	1056.4
12.5°	1014.3
15°	960.8
17.5°	906.1
20°	840.1
22.5°	772.7
25°	695.4
27.5°	611.1
30°	517.0
32.5°	414.5
35°	316.1
37.5°	229.0
40°	157.3
42.5°	101.2
45°	60.4
47.5°	33.8
50°	18.2
52.5°	9.9
55°	7.1
57.5°	5.6
60°	4.2
62.5°	4.2
65°	2.8
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)