

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211179

Luminaire Tested: **LE_4B15D010 EC4B10208030 4LBCSM1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211179
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208030 4LBSCM1B
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1694.5 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211179

CATALOG NUMBER: LE_4B15D010 EC4B10208030 4LBCSM1B

Luminous Intensity Polar Plot






TEST NUMBER: P211179

CATALOG NUMBER: LE_4B15D010 EC4B10208030 4LBCSM1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65		
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56		
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39		
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35		
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31		
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211179

CATALOG NUMBER: LE_4B15D010 EC4B10208030 4LBCSM1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.7	4.0
10°-20°	192.8	11.4
20°-30°	289.8	17.1
30°-40°	343.9	20.3
40°-50°	340.3	20.1
50°-60°	267.3	15.8
60°-70°	149.9	8.8
70°-80°	42.1	2.5
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	550.3	32.5
0°-40°	894.3	52.8
0°-60°	1501.9	88.6
0°-90°	1694.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1694.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	716	
5°	714	68
15°	684	193
25°	629	290
35°	552	344
45°	443	340
55°	301	267
65°	149	150
75°	36	42
85°	0	1
90°	0	



TEST NUMBER: P211179

CATALOG NUMBER: LE_4B15D010 EC4B10208030 4LBCSM1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	715.5
2.5°	713.1
5°	714.3
7.5°	708.3
10°	701.0
12.5°	692.4
15°	683.9
17.5°	673.0
20°	658.4
22.5°	643.8
25°	629.3
27.5°	613.5
30°	592.9
32.5°	572.2
35°	551.6
37.5°	527.2
40°	499.3
42.5°	472.6
45°	443.4
47.5°	410.6
50°	376.5
52.5°	337.7
55°	301.3
57.5°	260.0
60°	221.1
62.5°	185.8
65°	149.4
67.5°	117.9
70°	87.5
72.5°	59.5
75°	36.4
77.5°	18.2
80°	4.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)