

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211250

Luminaire Tested: **LE_4B15D010 EC4B10209730 4LBN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211250
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209730 4LBN1MW
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 923.4 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211250

CATALOG NUMBER: LE_4B15D010 EC4B10209730 4LBN1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211250

CATALOG NUMBER: LE_4B15D010 EC4B10209730 4LBN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	112	109	105	103	109	106	104	101		102	100	98			98	97	95			90
2	105	99	94	90	103	97	93	89		94	90	87			91	88	85			81
3	98	90	84	80	96	89	83	79		86	82	78			84	80	76			73
4	92	83	76	71	90	82	76	71		80	74	70			78	73	69			67
5	87	77	70	65	85	76	69	64		74	68	64			72	67	63			61
6	82	71	64	59	80	70	64	59		69	63	58			67	62	58			56
7	77	66	59	54	75	65	59	54		64	58	54			63	57	53			52
8	73	62	55	50	71	61	55	50		60	54	50			59	53	49			48
9	69	58	51	46	68	57	51	46		56	50	46			55	50	46			44
10	65	54	48	43	64	54	47	43		53	47	43			52	47	43			41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211250

CATALOG NUMBER: LE_4B15D010 EC4B10209730 4LBN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.5	7.8
10°-20°	189.6	20.5
20°-30°	249.6	27.0
30°-40°	194.3	21.0
40°-50°	94.4	10.2
50°-60°	59.6	6.5
60°-70°	38.5	4.2
70°-80°	20.0	2.2
80°-90°	5.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	511.6	55.4
0°-40°	705.9	76.4
0°-60°	859.9	93.1
0°-90°	923.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	923.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	788	
5°	773	72
15°	676	190
25°	550	250
35°	311	194
45°	117	94
55°	66	60
65°	38	38
75°	19	20
85°	4	5
90°	0	



TEST NUMBER: P211250

CATALOG NUMBER: LE_4B15D010 EC4B10209730 4LBN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	787.8
2.5°	783.3
5°	773.0
7.5°	755.5
10°	732.0
12.5°	705.6
15°	676.3
17.5°	645.4
20°	613.2
22.5°	582.3
25°	550.1
27.5°	509.0
30°	453.3
32.5°	387.3
35°	311.0
37.5°	240.6
40°	186.3
42.5°	145.2
45°	117.4
47.5°	95.4
50°	83.6
52.5°	74.8
55°	66.0
57.5°	58.7
60°	51.4
62.5°	44.0
65°	38.2
67.5°	33.8
70°	27.8
72.5°	23.4
75°	19.0
77.5°	14.6
80°	10.3
82.5°	7.3
85°	4.4
87.5°	1.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)