

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210837

Luminaire Tested: **LE_4B10D010 EC4B10209030 4LBM1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210837
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209030 4LBM1LI
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 997.7 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210837

CATALOG NUMBER: LE_4B10D010 EC4B10209030 4LBM1LI

Luminous Intensity Polar Plot






TEST NUMBER: P210837

CATALOG NUMBER: LE_4B10D010 EC4B10209030 4LBM1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	64		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210837

CATALOG NUMBER: LE_4B10D010 EC4B10209030 4LBM1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.4	14.3
10°-20°	318.4	31.9
20°-30°	316.6	31.7
30°-40°	172.4	17.3
40°-50°	39.8	4.0
50°-60°	5.6	0.6
60°-70°	2.1	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	777.4	77.9
0°-40°	949.8	95.2
0°-60°	995.2	99.7
0°-90°	997.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	997.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1573	
5°	1540	142
15°	1149	318
25°	694	317
35°	267	172
45°	46	40
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P210837

CATALOG NUMBER: LE_4B10D010 EC4B10209030 4LBM1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1573.0
2.5°	1569.4
5°	1540.4
7.5°	1481.2
10°	1399.2
12.5°	1278.4
15°	1149.2
17.5°	1021.3
20°	895.8
22.5°	793.1
25°	694.1
27.5°	600.0
30°	493.7
32.5°	375.5
35°	266.8
37.5°	179.9
40°	117.0
42.5°	73.7
45°	45.8
47.5°	26.6
50°	13.2
52.5°	7.2
55°	6.0
57.5°	3.6
60°	3.6
62.5°	2.4
65°	2.4
67.5°	1.2
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)