

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211257

Luminaire Tested: **LE_4B15D010 EC4B10209730 4LBS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211257
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209730 4LBS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1325.6 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211257

CATALOG NUMBER: LE_4B15D010 EC4B10209730 4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211257

CATALOG NUMBER: LE_4B15D010 EC4B10209730 4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	66	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211257

CATALOG NUMBER: LE_4B15D010 EC4B10209730 4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	3.8
10°-20°	144.3	10.9
20°-30°	217.2	16.4
30°-40°	258.5	19.5
40°-50°	258.0	19.5
50°-60°	209.9	15.8
60°-70°	129.1	9.7
70°-80°	50.0	3.8
80°-90°	8.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	412.1	31.1
0°-40°	670.6	50.6
0°-60°	1138.5	85.9
0°-90°	1325.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1325.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	534	
5°	533	51
15°	512	144
25°	473	217
35°	414	259
45°	335	258
55°	235	210
65°	130	129
75°	46	50
85°	6	8
90°	0	



TEST NUMBER: P211257

CATALOG NUMBER: LE_4B15D010 EC4B10209730 4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	534.1
2.5°	534.9
5°	532.6
7.5°	529.4
10°	525.5
12.5°	518.4
15°	512.1
17.5°	502.7
20°	492.5
22.5°	483.0
25°	472.8
27.5°	458.7
30°	444.5
32.5°	431.2
35°	413.9
37.5°	395.1
40°	377.8
42.5°	356.6
45°	335.4
47.5°	312.6
50°	288.3
52.5°	263.1
55°	234.9
57.5°	207.4
60°	180.6
62.5°	154.7
65°	129.6
67.5°	106.0
70°	84.1
72.5°	63.6
75°	45.6
77.5°	29.8
80°	18.1
82.5°	11.0
85°	6.3
87.5°	3.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)