

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210867

Luminaire Tested: **LE_4B10D010 EC4B10209730 4LBM1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209730 4LBM1MW
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 727.5 lumens
Efficiency: N/A
Efficacy: 73.5 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210867

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBM1MW

Luminous Intensity Polar Plot





TEST NUMBER: P210867

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBM1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94
2	104	98	92	88	102	96	91	87	93	89	85		89	86	83		87
3	97	89	83	77	95	87	82	77	85	80	76		82	78	74		80
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74
5	85	75	67	62	83	74	67	62	72	66	61		70	65	61		68
6	80	69	62	56	78	68	61	56	66	60	56		65	59	55		63
7	75	64	57	52	74	63	56	51	62	56	51		60	55	51		59
8	71	59	52	47	69	59	52	47	58	51	47		56	51	47		55
9	67	55	48	44	66	55	48	44	54	48	44		53	47	43		52
10	63	52	45	41	62	51	45	41	51	45	40		50	44	40		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210867

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBM1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.2	7.0
10°-20°	137.2	18.9
20°-30°	182.5	25.1
30°-40°	149.2	20.5
40°-50°	86.9	11.9
50°-60°	57.7	7.9
60°-70°	37.9	5.2
70°-80°	20.0	2.8
80°-90°	4.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.9	51.0
0°-40°	520.1	71.5
0°-60°	664.7	91.4
0°-90°	727.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	727.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	552	
5°	546	51
15°	489	137
25°	400	182
35°	238	149
45°	110	87
55°	64	58
65°	38	38
75°	19	20
85°	4	5
90°	0	



TEST NUMBER: P210867

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBM1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	552.3
2.5°	551.1
5°	545.9
7.5°	533.3
10°	519.6
12.5°	506.9
15°	488.9
17.5°	469.0
20°	452.1
22.5°	429.0
25°	400.4
27.5°	369.9
30°	330.9
32.5°	284.5
35°	238.1
37.5°	196.0
40°	159.2
42.5°	130.7
45°	109.6
47.5°	92.7
50°	81.2
52.5°	71.7
55°	64.3
57.5°	57.0
60°	49.5
62.5°	44.3
65°	37.9
67.5°	32.7
70°	27.4
72.5°	23.2
75°	19.0
77.5°	14.7
80°	10.6
82.5°	7.4
85°	4.2
87.5°	1.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)