

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210868

Luminaire Tested: **LE_4B10D010 EC4B10209730 4LBM1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209730 4LBM1WH
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 713.6 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210868

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBM1WH

Luminous Intensity Polar Plot





TEST NUMBER: P210868

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBM1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210868

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBM1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.3	11.0
10°-20°	201.3	28.2
20°-30°	236.2	33.1
30°-40°	149.5	20.9
40°-50°	40.0	5.6
50°-60°	5.6	0.8
60°-70°	2.0	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	515.9	72.3
0°-40°	665.3	93.2
0°-60°	711.0	99.6
0°-90°	713.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	713.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	848	
5°	834	78
15°	721	201
25°	522	236
35°	237	149
45°	45	40
55°	5	6
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P210868

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBM1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	847.6
2.5°	844.5
5°	833.9
7.5°	817.1
10°	792.9
12.5°	761.2
15°	721.2
17.5°	680.0
20°	630.5
22.5°	579.9
25°	521.9
27.5°	458.7
30°	388.0
32.5°	311.0
35°	237.2
37.5°	171.8
40°	118.1
42.5°	75.9
45°	45.4
47.5°	25.3
50°	13.7
52.5°	7.4
55°	5.2
57.5°	4.2
60°	3.1
62.5°	3.1
65°	2.1
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)