

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210872

Luminaire Tested: **LE_4B10D010 EC4B10209730 4LBN1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210872
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209730 4LBN1LI
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 684.1 lumens
Efficiency: N/A
Efficacy: 69.1 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210872

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBN1LI

Luminous Intensity Polar Plot






TEST NUMBER: P210872

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBN1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			99
2	109	105	102	99	107	103	100	98		100	98	95			97	95	93			95
3	105	99	95	92	103	98	94	91		95	92	89			93	90	88			91
4	101	94	89	86	99	93	88	85		91	87	84			89	86	83			87
5	96	89	84	80	95	88	84	80		87	82	79			85	81	79			83
6	92	85	80	76	91	84	79	76		83	78	75			81	78	75			80
7	89	81	76	72	88	80	75	72		79	75	71			78	74	71			77
8	85	77	72	68	84	77	72	68		76	71	68			75	71	68			74
9	82	74	69	65	81	73	68	65		72	68	65			72	68	65			71
10	79	71	66	62	78	70	65	62		69	65	62			69	65	62			68

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210872

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBN1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.8	20.3
10°-20°	237.6	34.7
20°-30°	188.8	27.6
30°-40°	99.9	14.6
40°-50°	17.2	2.5
50°-60°	1.3	0.2
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.1	82.6
0°-40°	665.0	97.2
0°-60°	683.5	99.9
0°-90°	684.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	684.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1761	
5°	1578	139
15°	859	238
25°	407	189
35°	158	100
45°	18	17
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P210872

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBN1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1760.8
2.5°	1715.5
5°	1578.5
7.5°	1399.3
10°	1209.6
12.5°	1026.4
15°	858.7
17.5°	702.8
20°	578.5
22.5°	483.7
25°	406.7
27.5°	344.5
30°	282.3
32.5°	219.1
35°	158.1
37.5°	104.3
40°	62.2
42.5°	35.8
45°	17.9
47.5°	6.4
50°	2.1
52.5°	2.1
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)