

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211338

Luminaire Tested: **LE_4B15D010 EC4B10208040 4LBN1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211338
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208040 4LBN1WH
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1180.0 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211338

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBN1WH

Luminous Intensity Polar Plot





TEST NUMBER: P211338

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBN1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	111	109	107		112	109	107	105		105	104	102			102	100	99			95
2	109	105	101	98		107	103	100	97		100	97	95			97	95	93			89
3	104	98	94	90		102	97	93	90		94	91	88			92	89	87			84
4	100	93	88	84		98	92	87	83		90	86	82			88	84	82			79
5	95	88	82	78		94	87	82	78		85	81	77			83	80	77			75
6	91	83	78	74		90	82	77	74		81	76	73			79	76	73			71
7	87	79	73	70		86	78	73	69		77	72	69			76	72	69			67
8	84	75	70	66		82	74	69	66		73	69	65			72	68	65			64
9	80	71	66	62		79	71	66	62		70	65	62			69	65	62			61
10	77	68	63	59		76	68	63	59		67	62	59			66	62	59			58

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211338

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBN1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.1	17.4
10°-20°	384.7	32.6
20°-30°	345.1	29.2
30°-40°	198.0	16.8
40°-50°	39.5	3.3
50°-60°	5.0	0.4
60°-70°	2.3	0.2
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	934.8	79.2
0°-40°	1132.9	96.0
0°-60°	1177.4	99.8
0°-90°	1180.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1180.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2508	
5°	2306	205
15°	1381	385
25°	746	345
35°	314	198
45°	43	40
55°	6	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211338

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBN1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2507.7
2.5°	2456.8
5°	2306.0
7.5°	2085.9
10°	1845.6
12.5°	1609.3
15°	1381.1
17.5°	1181.5
20°	1010.4
22.5°	867.8
25°	745.5
27.5°	647.7
30°	539.9
32.5°	429.8
35°	313.7
37.5°	213.9
40°	132.4
42.5°	79.5
45°	42.8
47.5°	18.3
50°	8.1
52.5°	6.1
55°	6.1
57.5°	4.1
60°	4.1
62.5°	2.1
65°	2.1
67.5°	2.1
70°	2.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)