

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210882

Luminaire Tested: **LE_4B10D010 EC4B10209730 4LBS1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210882
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209730 4LBS1WMH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 925.5 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210882

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBS1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P210882

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBS1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	102		109	106	103	101		102	100	97		98	96	94		95	93	92
2	104	98	92	88		102	96	91	87		92	88	85		89	86	83		86	84	81
3	96	88	82	76		94	87	81	76		84	79	74		81	77	73		79	75	72
4	90	80	73	67		88	79	72	67		76	70	66		74	69	65		72	68	64
5	83	73	65	59		82	72	64	59		70	63	59		68	62	58		66	61	57
6	78	66	59	53		76	65	58	53		64	57	53		62	57	52		61	56	52
7	73	61	53	48		71	60	53	48		59	52	48		57	52	47		56	51	47
8	68	56	49	44		67	56	48	43		54	48	43		53	47	43		52	47	43
9	64	52	45	40		63	52	45	40		50	44	40		49	44	39		49	43	39
10	60	48	41	37		59	48	41	37		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210882

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBS1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	5.9
10°-20°	143.7	15.5
20°-30°	193.0	20.8
30°-40°	197.5	21.3
40°-50°	170.9	18.5
50°-60°	113.7	12.3
60°-70°	46.7	5.0
70°-80°	5.5	0.6
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	390.8	42.2
0°-40°	588.3	63.6
0°-60°	873.0	94.3
0°-90°	925.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	925.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	587	
5°	577	54
15°	513	144
25°	421	193
35°	315	198
45°	223	171
55°	126	114
65°	46	47
75°	2	6
85°	0	0
90°	0	



TEST NUMBER: P210882

CATALOG NUMBER: LE_4B10D010 EC4B10209730 4LBS1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	586.6
2.5°	585.3
5°	577.4
7.5°	565.4
10°	548.9
12.5°	530.8
15°	513.2
17.5°	490.7
20°	468.9
22.5°	445.9
25°	421.0
27.5°	394.3
30°	367.6
32.5°	340.9
35°	315.4
37.5°	291.2
40°	268.1
42.5°	245.1
45°	222.6
47.5°	198.9
50°	174.7
52.5°	150.5
55°	126.2
57.5°	105.0
60°	83.1
62.5°	63.1
65°	46.1
67.5°	30.3
70°	17.6
72.5°	8.5
75°	2.4
77.5°	1.2
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)