

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211386

Luminaire Tested: **LE_4B15D010 EC4B10208050 4LBM1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208050 4LBM1GPH
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 969.6 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211386

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBM1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P211386

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBM1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	101		100	99	98		97	96	95
2	107	102	98	94		105	100	97	93		97	94	91		94	92	89		91	89	88
3	102	95	90	85		100	93	89	85		91	87	83		88	85	82		86	83	81
4	96	88	82	78		94	87	82	78		85	80	77		83	79	76		81	78	75
5	91	82	76	72		89	81	76	71		79	74	71		78	73	70		76	72	69
6	86	77	71	66		85	76	70	66		74	69	65		73	68	65		72	68	64
7	82	72	66	61		80	71	65	61		70	65	61		69	64	60		68	63	60
8	77	67	61	57		76	67	61	57		66	60	57		65	60	56		64	59	56
9	73	63	57	53		72	63	57	53		62	57	53		61	56	53		60	56	52
10	70	60	54	50		69	59	54	50		59	53	50		58	53	49		57	52	49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211386

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBM1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.7	9.5
10°-20°	239.2	24.7
20°-30°	306.8	31.6
30°-40°	221.7	22.9
40°-50°	79.5	8.2
50°-60°	21.5	2.2
60°-70°	7.0	0.7
70°-80°	2.2	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	637.7	65.8
0°-40°	859.4	88.6
0°-60°	960.4	99.0
0°-90°	969.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	969.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	997	
5°	978	92
15°	852	239
25°	677	307
35°	355	222
45°	96	80
55°	22	21
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P211386

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBM1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	996.8
2.5°	992.6
5°	978.3
7.5°	956.0
10°	925.4
12.5°	890.8
15°	852.0
17.5°	813.3
20°	774.5
22.5°	729.8
25°	676.7
27.5°	615.6
30°	538.1
32.5°	448.5
35°	354.6
37.5°	269.0
40°	195.7
42.5°	138.6
45°	95.8
47.5°	65.2
50°	42.8
52.5°	30.6
55°	22.4
57.5°	16.4
60°	12.2
62.5°	10.2
65°	6.1
67.5°	4.1
70°	4.1
72.5°	2.1
75°	2.1
77.5°	2.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)