

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210889

Luminaire Tested: **LE_4B10D010 EC4B10208035 4LBCSM1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210889
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208035 4LBSCM1B
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1247.1 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210889

CATALOG NUMBER: LE_4B10D010 EC4B10208035 4LBCSM1B

Luminous Intensity Polar Plot





TEST NUMBER: P210889

CATALOG NUMBER: LE_4B10D010 EC4B10208035 4LBCSM1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	104	101	98		100	98	95		96	94	92		93	91	90
2	102	95	89	84		99	93	87	83		89	85	81		86	82	79		83	80	77
3	93	84	77	71		91	83	76	70		80	74	69		77	72	68		74	70	67
4	86	75	67	61		84	74	66	61		71	65	60		69	63	59		67	62	58
5	79	67	59	53		77	66	59	53		64	57	52		62	56	52		61	55	51
6	74	61	53	47		72	60	52	46		58	51	46		57	50	46		55	50	45
7	68	55	47	41		67	55	47	41		53	46	41		52	45	41		50	45	40
8	64	51	43	37		62	50	42	37		49	42	37		48	41	37		46	41	36
9	60	47	39	33		58	46	39	33		45	38	33		44	38	33		43	37	33
10	56	43	35	30		55	43	35	30		42	35	30		41	34	30		40	34	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210889

CATALOG NUMBER: LE_4B10D010 EC4B10208035 4LBCSM1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.8	4.0
10°-20°	141.9	11.4
20°-30°	213.3	17.1
30°-40°	253.1	20.3
40°-50°	250.5	20.1
50°-60°	196.7	15.8
60°-70°	110.3	8.8
70°-80°	31.0	2.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.0	32.5
0°-40°	658.1	52.8
0°-60°	1105.3	88.6
0°-90°	1247.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1247.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	526	
5°	526	50
15°	503	142
25°	463	213
35°	406	253
45°	326	250
55°	222	197
65°	110	110
75°	27	31
85°	0	0
90°	0	



TEST NUMBER: P210889

CATALOG NUMBER: LE_4B10D010 EC4B10208035 4LBCSM1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	526.5
2.5°	524.8
5°	525.7
7.5°	521.2
10°	515.9
12.5°	509.6
15°	503.3
17.5°	495.3
20°	484.5
22.5°	473.9
25°	463.1
27.5°	451.5
30°	436.3
32.5°	421.1
35°	405.9
37.5°	388.0
40°	367.5
42.5°	347.8
45°	326.3
47.5°	302.2
50°	277.1
52.5°	248.6
55°	221.7
57.5°	191.3
60°	162.7
62.5°	136.8
65°	110.0
67.5°	86.8
70°	64.4
72.5°	43.8
75°	26.8
77.5°	13.5
80°	3.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)