

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210935

Luminaire Tested: **LE_4B10D010 EC4B10209035 4LBS1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210935
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209035 4LBS1GPH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 972.7 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210935

CATALOG NUMBER: LE_4B10D010 EC4B10209035 4LBS1GPH

Luminous Intensity Polar Plot






TEST NUMBER: P210935

CATALOG NUMBER: LE_4B10D010 EC4B10209035 4LBS1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	105	102	99		101	98	96		97	95	93		93	92	90
2	102	95	89	84		100	93	88	83		90	85	82		87	83	80		84	81	78
3	94	85	78	72		92	83	77	71		80	75	70		78	73	69		75	71	68
4	87	76	68	62		85	75	67	62		72	66	61		70	65	60		68	63	59
5	80	68	60	54		78	67	60	54		65	59	53		63	58	53		62	56	52
6	74	62	54	48		73	61	53	48		59	52	47		58	52	47		56	51	47
7	69	57	48	43		68	56	48	43		54	47	42		53	47	42		52	46	42
8	65	52	44	38		63	51	44	38		50	43	38		49	42	38		48	42	38
9	60	48	40	35		59	47	40	35		46	39	35		45	39	34		44	38	34
10	57	44	37	32		56	44	36	32		43	36	32		42	36	31		41	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210935

CATALOG NUMBER: LE_4B10D010 EC4B10209035 4LBS1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.5	4.4
10°-20°	119.4	12.3
20°-30°	174.2	17.9
30°-40°	198.6	20.4
40°-50°	190.5	19.6
50°-60°	145.9	15.0
60°-70°	80.0	8.2
70°-80°	21.3	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.1	34.6
0°-40°	534.7	55.0
0°-60°	871.1	89.6
0°-90°	972.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	972.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	452	
5°	448	43
15°	424	119
25°	378	174
35°	318	199
45°	248	191
55°	163	146
65°	80	80
75°	19	21
85°	0	0
90°	0	



TEST NUMBER: P210935

CATALOG NUMBER: LE_4B10D010 EC4B10209035 4LBS1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	451.8
2.5°	450.7
5°	448.3
7.5°	444.7
10°	440.1
12.5°	432.0
15°	423.7
17.5°	414.5
20°	403.9
22.5°	391.2
25°	378.3
27.5°	365.4
30°	349.0
32.5°	333.8
35°	317.5
37.5°	301.3
40°	284.9
42.5°	267.4
45°	247.5
47.5°	227.7
50°	206.6
52.5°	184.4
55°	163.4
57.5°	142.4
60°	120.3
62.5°	99.2
65°	80.5
67.5°	61.8
70°	45.6
72.5°	30.4
75°	18.7
77.5°	8.1
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)