

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211406

Luminaire Tested: **LE_4B15D010 EC4B10208050 4LBW1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208050 4LBW1GPH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1175.2 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211406

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBW1GPH

Luminous Intensity Polar Plot






TEST NUMBER: P211406

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBW1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	99		100	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	72	65	61	81	71	65	60	70	64	60		68	63	59		67
7	78	67	60	55	76	66	60	55	65	59	55		64	58	55		63
8	73	62	56	51	72	62	55	51	61	55	51		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	54	48	43	64	54	48	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211406

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBW1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.8	6.8
10°-20°	226.1	19.2
20°-30°	324.3	27.6
30°-40°	305.3	26.0
40°-50°	168.6	14.3
50°-60°	54.1	4.6
60°-70°	13.5	1.1
70°-80°	3.3	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	630.1	53.6
0°-40°	935.5	79.6
0°-60°	1158.2	98.6
0°-90°	1175.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1175.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	846	
5°	842	80
15°	801	226
25°	711	324
35°	495	305
45°	214	169
55°	55	54
65°	12	13
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P211406

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBW1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	845.9
2.5°	839.7
5°	841.8
7.5°	835.7
10°	825.5
12.5°	815.2
15°	801.0
17.5°	788.8
20°	768.4
22.5°	739.8
25°	711.3
27.5°	672.6
30°	621.6
32.5°	564.6
35°	495.3
37.5°	421.9
40°	346.5
42.5°	277.2
45°	214.0
47.5°	161.0
50°	116.2
52.5°	81.5
55°	55.0
57.5°	36.7
60°	26.4
62.5°	18.3
65°	12.2
67.5°	8.1
70°	6.1
72.5°	4.1
75°	2.1
77.5°	2.1
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)