

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210942

Luminaire Tested: **LE_4B10D010 EC4B10209035 4LBW1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210942
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209035 4LBW1GPH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 706.6 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210942

CATALOG NUMBER: LE_4B10D010 EC4B10209035 4LBW1GPH

Luminous Intensity Polar Plot






TEST NUMBER: P210942

CATALOG NUMBER: LE_4B10D010 EC4B10209035 4LBW1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	99		100	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	72	65	61	81	71	65	60	70	64	60		68	63	59		67
7	78	67	60	55	76	66	60	55	65	59	55		64	58	55		63
8	73	62	56	51	72	62	55	51	61	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	54	48	43	64	54	48	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210942

CATALOG NUMBER: LE_4B10D010 EC4B10209035 4LBW1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.0	6.8
10°-20°	135.9	19.2
20°-30°	195.0	27.6
30°-40°	183.6	26.0
40°-50°	101.4	14.3
50°-60°	32.5	4.6
60°-70°	8.1	1.1
70°-80°	2.0	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	378.9	53.6
0°-40°	562.4	79.6
0°-60°	696.3	98.5
0°-90°	706.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	706.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	508	
5°	506	48
15°	482	136
25°	428	195
35°	298	184
45°	129	101
55°	33	33
65°	7	8
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P210942

CATALOG NUMBER: LE_4B10D010 EC4B10209035 4LBW1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	508.5
2.5°	504.8
5°	506.1
7.5°	502.4
10°	496.2
12.5°	490.1
15°	481.5
17.5°	474.2
20°	461.9
22.5°	444.9
25°	427.7
27.5°	404.4
30°	373.8
32.5°	339.4
35°	297.8
37.5°	253.7
40°	208.3
42.5°	166.7
45°	128.6
47.5°	96.9
50°	69.8
52.5°	49.1
55°	33.1
57.5°	22.0
60°	15.9
62.5°	11.0
65°	7.3
67.5°	4.9
70°	3.7
72.5°	2.4
75°	1.3
77.5°	1.3
80°	1.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)