

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210976

Luminaire Tested: **LE_4B10D010 EC4B10209040 4LBCSM1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209040 4LBSCM1B
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1055.8 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210976

CATALOG NUMBER: LE_4B10D010 EC4B10209040 4LBCSM1B

Luminous Intensity Polar Plot





TEST NUMBER: P210976

CATALOG NUMBER: LE_4B10D010 EC4B10209040 4LBCSM1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65		
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56		
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39		
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35		
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31		
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210976

CATALOG NUMBER: LE_4B10D010 EC4B10209040 4LBCSM1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.2	4.0
10°-20°	120.1	11.4
20°-30°	180.6	17.1
30°-40°	214.3	20.3
40°-50°	212.0	20.1
50°-60°	166.5	15.8
60°-70°	93.4	8.8
70°-80°	26.2	2.5
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	342.9	32.5
0°-40°	557.1	52.8
0°-60°	935.7	88.6
0°-90°	1055.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1055.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	446	
5°	445	42
15°	426	120
25°	392	181
35°	344	214
45°	276	212
55°	188	167
65°	93	93
75°	23	26
85°	0	0
90°	0	



TEST NUMBER: P210976

CATALOG NUMBER: LE_4B10D010 EC4B10209040 4LBCSM1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	445.8
2.5°	444.3
5°	445.1
7.5°	441.3
10°	436.7
12.5°	431.4
15°	426.1
17.5°	419.3
20°	410.2
22.5°	401.1
25°	392.1
27.5°	382.2
30°	369.3
32.5°	356.5
35°	343.6
37.5°	328.5
40°	311.1
42.5°	294.4
45°	276.3
47.5°	255.8
50°	234.7
52.5°	210.4
55°	187.7
57.5°	161.9
60°	137.8
62.5°	115.8
65°	93.1
67.5°	73.4
70°	54.5
72.5°	37.1
75°	22.7
77.5°	11.4
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)