

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211002

Luminaire Tested: **LE_4B10D010 EC4B10209040 4LBW1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211002
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209040 4LBW1LI
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1069.9 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211002

CATALOG NUMBER: LE_4B10D010 EC4B10209040 4LBW1LI

Luminous Intensity Polar Plot






TEST NUMBER: P211002

CATALOG NUMBER: LE_4B10D010 EC4B10209040 4LBW1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211002

CATALOG NUMBER: LE_4B10D010 EC4B10209040 4LBW1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.1	6.0
10°-20°	202.3	18.9
20°-30°	315.6	29.5
30°-40°	307.1	28.7
40°-50°	153.4	14.3
50°-60°	23.8	2.2
60°-70°	2.9	0.3
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.0	54.4
0°-40°	889.1	83.1
0°-60°	1066.2	99.7
0°-90°	1069.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1069.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	656	
5°	664	64
15°	714	202
25°	694	316
35°	499	307
45°	192	153
55°	20	24
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P211002

CATALOG NUMBER: LE_4B10D010 EC4B10209040 4LBW1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	655.5
2.5°	658.0
5°	664.1
7.5°	674.0
10°	686.1
12.5°	702.1
15°	714.3
17.5°	724.2
20°	725.3
22.5°	716.9
25°	693.6
27.5°	659.2
30°	616.3
32.5°	562.5
35°	498.7
37.5°	428.9
40°	355.3
42.5°	276.9
45°	192.3
47.5°	123.8
50°	74.7
52.5°	40.5
55°	19.6
57.5°	8.6
60°	4.9
62.5°	3.7
65°	2.4
67.5°	2.4
70°	1.3
72.5°	1.3
75°	1.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)