

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211444

Luminaire Tested: **LE_4B20D010 EC4B10209024 4LBM1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211444
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209024 4LBM1GPH
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 916.4 lumens
Efficiency: N/A
Efficacy: 44.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211444

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBM1GPH

Luminous Intensity Polar Plot






TEST NUMBER: P211444

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBM1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93		
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86		
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73		
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68		
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211444

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBM1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	9.5
10°-20°	226.1	24.7
20°-30°	290.0	31.6
30°-40°	209.6	22.9
40°-50°	75.1	8.2
50°-60°	20.3	2.2
60°-70°	6.6	0.7
70°-80°	2.1	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	602.7	65.8
0°-40°	812.2	88.6
0°-60°	907.7	99.1
0°-90°	916.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	916.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	942	
5°	925	87
15°	805	226
25°	640	290
35°	335	210
45°	91	75
55°	21	20
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P211444

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBM1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	942.0
2.5°	938.2
5°	924.8
7.5°	903.5
10°	874.6
12.5°	841.9
15°	805.3
17.5°	768.6
20°	732.1
22.5°	689.7
25°	639.6
27.5°	581.9
30°	508.5
32.5°	423.9
35°	335.2
37.5°	254.3
40°	184.9
42.5°	131.0
45°	90.6
47.5°	61.6
50°	40.5
52.5°	28.9
55°	21.2
57.5°	15.4
60°	11.6
62.5°	9.6
65°	5.8
67.5°	3.8
70°	3.8
72.5°	2.0
75°	2.0
77.5°	2.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)