

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211455

Luminaire Tested: **LE_4B20D010 EC4B10209024 4LBPS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209024 4LBPS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1809.6 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211455

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBPS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211455

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBPS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63		
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47		
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42		
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37		
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33		
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30		
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211455

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBPS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	3.8
10°-20°	196.9	10.9
20°-30°	296.6	16.4
30°-40°	352.9	19.5
40°-50°	352.3	19.5
50°-60°	286.4	15.8
60°-70°	176.2	9.7
70°-80°	68.3	3.8
80°-90°	10.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	562.6	31.1
0°-40°	915.5	50.6
0°-60°	1554.1	85.9
0°-90°	1809.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1809.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	729	
5°	727	69
15°	699	197
25°	645	297
35°	565	353
45°	458	352
55°	321	286
65°	177	176
75°	62	68
85°	9	11
90°	0	



TEST NUMBER: P211455

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBPS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	729.1
2.5°	730.2
5°	727.0
7.5°	722.7
10°	717.3
12.5°	707.6
15°	699.1
17.5°	686.3
20°	672.2
22.5°	659.5
25°	645.4
27.5°	626.2
30°	606.9
32.5°	588.6
35°	565.0
37.5°	539.3
40°	515.7
42.5°	486.7
45°	457.9
47.5°	426.8
50°	393.5
52.5°	359.1
55°	320.6
57.5°	283.0
60°	246.6
62.5°	211.2
65°	176.9
67.5°	144.8
70°	114.7
72.5°	86.9
75°	62.2
77.5°	40.7
80°	24.7
82.5°	15.0
85°	8.6
87.5°	4.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)