

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211076

Luminaire Tested: **LE_4B15D010 EC4B10209024 4LBN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209024 4LBN1MW
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 894.4 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211076

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBN1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211076

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	80	96	89	83	79	86	82	78		84	80	76		81
4	92	83	76	71	90	82	76	71	80	74	70		78	73	69		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62
8	73	62	55	50	71	61	55	50	60	54	50		59	53	49		58
9	69	58	51	46	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	43	64	54	47	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211076

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.2	7.8
10°-20°	183.7	20.5
20°-30°	241.7	27.0
30°-40°	188.2	21.0
40°-50°	91.4	10.2
50°-60°	57.7	6.5
60°-70°	37.2	4.2
70°-80°	19.5	2.2
80°-90°	4.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	495.6	55.4
0°-40°	683.7	76.4
0°-60°	832.9	93.1
0°-90°	894.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	894.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	763	
5°	749	70
15°	655	184
25°	533	242
35°	301	188
45°	114	91
55°	64	58
65°	37	37
75°	18	19
85°	4	5
90°	0	



TEST NUMBER: P211076

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	762.9
2.5°	758.8
5°	748.8
7.5°	731.7
10°	709.0
12.5°	683.4
15°	655.1
17.5°	625.1
20°	593.9
22.5°	564.1
25°	532.8
27.5°	493.0
30°	439.1
32.5°	375.1
35°	301.3
37.5°	233.0
40°	180.5
42.5°	140.7
45°	113.7
47.5°	92.3
50°	81.0
52.5°	72.5
55°	63.9
57.5°	56.8
60°	49.8
62.5°	42.6
65°	36.9
67.5°	32.7
70°	27.0
72.5°	22.7
75°	18.4
77.5°	14.2
80°	10.0
82.5°	7.1
85°	4.3
87.5°	1.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)