

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211080

Luminaire Tested: **LE_4B15D010 EC4B10209024 4LBS1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211080
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209024 4LBS1GPH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1129.6 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211080

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBS1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P211080

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBS1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	105	102	99	101	98	96		97	95	93		93
2	102	95	89	84	100	93	88	83	90	85	82		87	83	80		84
3	94	85	78	72	92	83	77	71	80	75	70		78	73	69		75
4	87	76	68	62	85	75	67	62	72	66	61		70	65	60		68
5	80	68	60	54	78	67	60	54	65	59	53		63	58	53		62
6	74	62	54	48	73	61	53	48	59	52	47		58	52	47		56
7	69	57	48	43	68	56	48	43	54	47	42		53	47	42		52
8	65	52	44	38	63	51	44	38	50	43	38		49	42	38		48
9	60	48	40	35	59	47	40	35	46	39	35		45	39	34		44
10	57	44	37	32	56	44	36	32	43	36	31		42	36	31		41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211080

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBS1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.4	4.4
10°-20°	138.7	12.3
20°-30°	202.2	17.9
30°-40°	230.6	20.4
40°-50°	221.2	19.6
50°-60°	169.5	15.0
60°-70°	93.0	8.2
70°-80°	24.7	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	390.3	34.5
0°-40°	620.9	55.0
0°-60°	1011.6	89.5
0°-90°	1129.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1129.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	525	
5°	521	49
15°	492	139
25°	439	202
35°	369	231
45°	287	221
55°	190	169
65°	94	93
75°	22	25
85°	0	0
90°	0	



TEST NUMBER: P211080

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBS1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	524.7
2.5°	523.3
5°	520.6
7.5°	516.5
10°	511.1
12.5°	501.6
15°	492.1
17.5°	481.3
20°	469.1
22.5°	454.1
25°	439.3
27.5°	424.3
30°	405.3
32.5°	387.7
35°	368.8
37.5°	349.7
40°	330.8
42.5°	310.4
45°	287.4
47.5°	264.4
50°	240.0
52.5°	214.3
55°	189.8
57.5°	165.4
60°	139.7
62.5°	115.2
65°	93.5
67.5°	71.8
70°	52.9
72.5°	35.3
75°	21.7
77.5°	9.5
80°	2.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)