

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211460

Luminaire Tested: **LE_4B20D010 EC4B10209024 4LBS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211460
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209024 4LBS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1738.3 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211460

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBS1MW

Luminous Intensity Polar Plot






TEST NUMBER: P211460

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	66	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211460

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.4	3.8
10°-20°	189.2	10.9
20°-30°	284.9	16.4
30°-40°	339.0	19.5
40°-50°	338.4	19.5
50°-60°	275.2	15.8
60°-70°	169.3	9.7
70°-80°	65.6	3.8
80°-90°	10.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	540.4	31.1
0°-40°	879.4	50.6
0°-60°	1493.0	85.9
0°-90°	1738.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1738.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	700	
5°	698	66
15°	672	189
25°	620	285
35°	543	339
45°	440	338
55°	308	275
65°	170	169
75°	60	66
85°	8	11
90°	0	



TEST NUMBER: P211460

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	700.4
2.5°	701.5
5°	698.3
7.5°	694.3
10°	689.0
12.5°	679.8
15°	671.5
17.5°	659.2
20°	645.8
22.5°	633.5
25°	620.0
27.5°	601.5
30°	583.0
32.5°	565.5
35°	542.8
37.5°	518.1
40°	495.4
42.5°	467.6
45°	439.8
47.5°	409.9
50°	378.0
52.5°	345.0
55°	308.0
57.5°	271.9
60°	236.9
62.5°	202.9
65°	169.9
67.5°	139.1
70°	110.2
72.5°	83.4
75°	59.7
77.5°	39.1
80°	23.7
82.5°	14.4
85°	8.2
87.5°	4.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)