

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211083

Luminaire Tested: **LE_4B15D010 EC4B10209024 4LBS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211083
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209024 4LBS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1283.9 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211083

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211083

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	66	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211083

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	3.8
10°-20°	139.7	10.9
20°-30°	210.4	16.4
30°-40°	250.4	19.5
40°-50°	249.9	19.5
50°-60°	203.3	15.8
60°-70°	125.0	9.7
70°-80°	48.4	3.8
80°-90°	7.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	399.2	31.1
0°-40°	649.6	50.6
0°-60°	1102.7	85.9
0°-90°	1283.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1283.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	517	
5°	516	49
15°	496	140
25°	458	210
35°	401	250
45°	325	250
55°	228	203
65°	126	125
75°	44	48
85°	6	8
90°	0	



TEST NUMBER: P211083

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	517.4
2.5°	518.1
5°	515.9
7.5°	512.7
10°	509.0
12.5°	502.0
15°	496.0
17.5°	486.9
20°	477.0
22.5°	467.8
25°	458.0
27.5°	444.3
30°	430.6
32.5°	417.7
35°	400.9
37.5°	382.7
40°	366.0
42.5°	345.3
45°	324.8
47.5°	302.8
50°	279.2
52.5°	254.9
55°	227.5
57.5°	200.8
60°	174.9
62.5°	149.9
65°	125.5
67.5°	102.7
70°	81.4
72.5°	61.6
75°	44.1
77.5°	28.9
80°	17.5
82.5°	10.7
85°	6.0
87.5°	3.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)