

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211087

Luminaire Tested: **LE_4B15D010 EC4B10209024 4LBW1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211087
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209024 4LBW1GPH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 820.5 lumens
Efficiency: N/A
Efficacy: 57.4 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211087

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBW1GPH

Luminous Intensity Polar Plot






TEST NUMBER: P211087

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBW1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	99		100	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	72	65	61	81	71	65	60	70	64	60		68	63	59		67
7	78	67	60	55	76	66	60	55	65	59	55		64	58	55		63
8	73	62	56	51	72	62	55	51	61	55	51		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	54	48	43	64	54	48	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211087

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBW1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.7	6.8
10°-20°	157.9	19.2
20°-30°	226.4	27.6
30°-40°	213.2	26.0
40°-50°	117.7	14.3
50°-60°	37.8	4.6
60°-70°	9.5	1.2
70°-80°	2.2	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	439.9	53.6
0°-40°	653.1	79.6
0°-60°	808.6	98.6
0°-90°	820.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	820.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	591	
5°	588	56
15°	559	158
25°	497	226
35°	346	213
45°	149	118
55°	38	38
65°	9	9
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P211087

CATALOG NUMBER: LE_4B15D010 EC4B10209024 4LBW1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	590.6
2.5°	586.3
5°	587.7
7.5°	583.4
10°	576.3
12.5°	569.2
15°	559.2
17.5°	550.7
20°	536.4
22.5°	516.5
25°	496.6
27.5°	469.6
30°	434.0
32.5°	394.2
35°	345.8
37.5°	294.5
40°	241.9
42.5°	193.5
45°	149.4
47.5°	112.4
50°	81.1
52.5°	57.0
55°	38.4
57.5°	25.6
60°	18.4
62.5°	12.8
65°	8.6
67.5°	5.7
70°	4.3
72.5°	2.9
75°	1.4
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)