

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211223

Luminaire Tested: **LE_4B15D010 EC4B10209030 4LBPS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211223
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209030 4LBPS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1579.7 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211223

CATALOG NUMBER: LE_4B15D010 EC4B10209030 4LBPS1MW

Luminous Intensity Polar Plot






TEST NUMBER: P211223

CATALOG NUMBER: LE_4B15D010 EC4B10209030 4LBPS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	65	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211223

CATALOG NUMBER: LE_4B15D010 EC4B10209030 4LBPS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.3	3.8
10°-20°	171.9	10.9
20°-30°	258.9	16.4
30°-40°	308.1	19.5
40°-50°	307.5	19.5
50°-60°	250.1	15.8
60°-70°	153.8	9.7
70°-80°	59.6	3.8
80°-90°	9.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	491.1	31.1
0°-40°	799.1	50.6
0°-60°	1356.7	85.9
0°-90°	1579.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1579.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	636	
5°	635	60
15°	610	172
25°	564	259
35°	493	308
45°	400	307
55°	280	250
65°	154	154
75°	54	60
85°	8	10
90°	0	



TEST NUMBER: P211223

CATALOG NUMBER: LE_4B15D010 EC4B10209030 4LBPS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	636.5
2.5°	637.4
5°	634.6
7.5°	630.8
10°	626.2
12.5°	617.8
15°	610.3
17.5°	599.0
20°	586.8
22.5°	575.6
25°	563.5
27.5°	546.6
30°	529.8
32.5°	513.9
35°	493.2
37.5°	470.8
40°	450.2
42.5°	424.9
45°	399.6
47.5°	372.5
50°	343.5
52.5°	313.5
55°	279.9
57.5°	247.1
60°	215.3
62.5°	184.4
65°	154.4
67.5°	126.3
70°	100.1
72.5°	75.9
75°	54.3
77.5°	35.6
80°	21.6
82.5°	13.1
85°	7.5
87.5°	3.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)