

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211647

Luminaire Tested: **LE_4B20D010 EC4B10208035 4LBM1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10208035 4LBM1GPH
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1299.7 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211647

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBM1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P211647

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBM1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	82	76	72	89	81	76	71	79	74	71		78	73	70		76
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	73	63	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	49		57

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211647

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBM1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.9	9.5
10°-20°	320.6	24.7
20°-30°	411.2	31.6
30°-40°	297.2	22.9
40°-50°	106.6	8.2
50°-60°	28.7	2.2
60°-70°	9.4	0.7
70°-80°	2.9	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	854.8	65.8
0°-40°	1152.1	88.6
0°-60°	1287.4	99.0
0°-90°	1299.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1299.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1336	
5°	1312	123
15°	1142	321
25°	907	411
35°	476	297
45°	128	107
55°	30	29
65°	8	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P211647

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBM1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1336.2
2.5°	1330.8
5°	1311.6
7.5°	1281.6
10°	1240.6
12.5°	1194.1
15°	1142.3
17.5°	1090.3
20°	1038.3
22.5°	978.2
25°	907.2
27.5°	825.2
30°	721.4
32.5°	601.1
35°	475.5
37.5°	360.6
40°	262.3
42.5°	185.8
45°	128.4
47.5°	87.5
50°	57.4
52.5°	40.9
55°	30.0
57.5°	21.8
60°	16.4
62.5°	13.7
65°	8.2
67.5°	5.5
70°	5.5
72.5°	2.8
75°	2.8
77.5°	2.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)