

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211651

Luminaire Tested: **LE_4B20D010 EC4B10208035 4LBM1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211651
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10208035 4LBM1WH
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1848.6 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211651

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBM1WH

Luminous Intensity Polar Plot





TEST NUMBER: P211651

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBM1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	105	105	103	101		101	100	98		98
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211651

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBM1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.8	11.0
10°-20°	521.4	28.2
20°-30°	611.8	33.1
30°-40°	387.1	20.9
40°-50°	103.7	5.6
50°-60°	14.5	0.8
60°-70°	5.4	0.3
70°-80°	1.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1336.0	72.3
0°-40°	1723.2	93.2
0°-60°	1841.3	99.6
0°-90°	1848.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1848.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2195	
5°	2160	203
15°	1868	521
25°	1352	612
35°	614	387
45°	117	104
55°	14	15
65°	6	5
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P211651

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBM1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2195.4
2.5°	2187.2
5°	2159.9
7.5°	2116.2
10°	2053.4
12.5°	1971.5
15°	1867.7
17.5°	1761.2
20°	1632.9
22.5°	1501.9
25°	1351.6
27.5°	1187.8
30°	1004.9
32.5°	805.5
35°	614.3
37.5°	445.1
40°	305.8
42.5°	196.6
45°	117.4
47.5°	65.5
50°	35.5
52.5°	19.1
55°	13.7
57.5°	10.9
60°	8.2
62.5°	8.2
65°	5.5
67.5°	2.8
70°	2.8
72.5°	2.8
75°	2.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)