

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211346

Luminaire Tested: **LE_4B15D010 EC4B10208040 4LBS1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211346
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208040 4LBS1WMH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1789.0 lumens
Efficiency: N/A
Efficacy: 125.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211346

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBS1WMH

Luminous Intensity Polar Plot






TEST NUMBER: P211346

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBS1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	102		109	106	103	101		102	100	97		98	96	94		95	93	92
2	104	98	92	88		102	96	91	87		92	88	85		89	86	83		86	84	81
3	96	88	82	76		94	87	81	76		84	79	74		81	77	73		79	75	72
4	90	80	73	67		88	79	72	67		76	70	66		74	69	65		72	68	64
5	83	73	65	59		82	72	64	59		70	63	59		68	62	58		66	61	57
6	78	66	59	53		76	65	58	53		64	57	53		62	57	52		61	56	52
7	73	61	53	48		71	60	53	48		59	52	48		57	52	47		56	51	47
8	68	56	49	44		67	56	48	43		54	48	43		53	47	43		52	47	43
9	64	52	45	40		63	52	45	40		50	44	40		49	44	39		49	43	39
10	60	48	41	37		59	48	41	37		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211346

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBS1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.8	5.9
10°-20°	277.7	15.5
20°-30°	373.0	20.8
30°-40°	381.8	21.3
40°-50°	330.5	18.5
50°-60°	219.8	12.3
60°-70°	90.3	5.0
70°-80°	10.7	0.6
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	755.5	42.2
0°-40°	1137.3	63.6
0°-60°	1687.6	94.3
0°-90°	1789.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1789.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1134	
5°	1116	105
15°	992	278
25°	814	373
35°	610	382
45°	430	330
55°	244	220
65°	89	90
75°	5	11
85°	0	0
90°	0	



TEST NUMBER: P211346

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBS1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1133.9
2.5°	1131.5
5°	1116.3
7.5°	1092.8
10°	1061.2
12.5°	1026.0
15°	992.0
17.5°	948.6
20°	906.4
22.5°	861.9
25°	813.7
27.5°	762.1
30°	710.6
32.5°	659.0
35°	609.7
37.5°	562.8
40°	518.3
42.5°	473.7
45°	430.4
47.5°	384.7
50°	337.7
52.5°	290.8
55°	243.9
57.5°	202.9
60°	160.7
62.5°	121.9
65°	89.1
67.5°	58.6
70°	34.0
72.5°	16.5
75°	4.6
77.5°	2.3
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)