

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211374

Luminaire Tested: **LE_4B15D010 EC4B10209040 4LBS1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211374
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209040 4LBS1WH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1486.5 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211374

CATALOG NUMBER: LE_4B15D010 EC4B10209040 4LBS1WH

Luminous Intensity Polar Plot





TEST NUMBER: P211374

CATALOG NUMBER: LE_4B15D010 EC4B10209040 4LBS1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	96	90	85	100	94	89	84	91	86	83		87	84	81		85
3	95	86	79	73	93	84	78	73	82	76	72		79	74	70		76
4	88	77	70	64	86	76	69	63	74	68	63		72	66	62		69
5	81	70	62	56	79	69	62	56	67	60	55		65	59	55		63
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58
7	71	58	51	45	69	58	50	45	56	49	45		55	49	44		54
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211374

CATALOG NUMBER: LE_4B15D010 EC4B10209040 4LBS1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.8	5.5
10°-20°	211.6	14.2
20°-30°	276.8	18.6
30°-40°	293.1	19.7
40°-50°	273.4	18.4
50°-60°	207.1	13.9
60°-70°	112.2	7.5
70°-80°	30.1	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	570.2	38.4
0°-40°	863.4	58.1
0°-60°	1343.8	90.4
0°-90°	1486.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1486.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	886	
5°	874	82
15°	756	212
25°	602	277
35°	468	293
45°	356	273
55°	233	207
65°	112	112
75°	26	30
85°	0	0
90°	0	



TEST NUMBER: P211374

CATALOG NUMBER: LE_4B15D010 EC4B10209040 4LBS1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	886.5
2.5°	883.2
5°	873.5
7.5°	852.4
10°	824.8
12.5°	792.2
15°	756.4
17.5°	715.7
20°	680.0
22.5°	639.3
25°	601.8
27.5°	564.5
30°	528.6
32.5°	497.8
35°	468.5
37.5°	439.2
40°	411.6
42.5°	383.8
45°	356.2
47.5°	325.4
50°	294.4
52.5°	263.6
55°	232.6
57.5°	200.1
60°	169.1
62.5°	139.9
65°	112.3
67.5°	86.2
70°	63.5
72.5°	44.0
75°	26.0
77.5°	11.4
80°	3.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)