

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211659

Luminaire Tested: **LE_4B20D010 EC4B10208035 4LBS1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211659
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10208035 4LBS1B
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2078.2 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211659

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBS1B

Luminous Intensity Polar Plot






TEST NUMBER: P211659

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76		
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65		
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44		
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211659

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.5	4.2
10°-20°	245.5	11.8
20°-30°	365.2	17.6
30°-40°	425.0	20.4
40°-50°	414.2	19.9
50°-60°	318.6	15.3
60°-70°	176.2	8.5
70°-80°	46.6	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	697.2	33.6
0°-40°	1122.2	54.0
0°-60°	1855.0	89.3
0°-90°	2078.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2078.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	917	
5°	912	87
15°	869	246
25°	793	365
35°	682	425
45°	537	414
55°	356	319
65°	177	176
75°	40	47
85°	0	0
90°	0	



TEST NUMBER: P211659

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	916.7
2.5°	916.7
5°	911.5
7.5°	903.5
10°	898.3
12.5°	882.5
15°	869.3
17.5°	856.2
20°	837.8
22.5°	819.3
25°	793.0
27.5°	766.6
30°	740.2
32.5°	711.3
35°	682.3
37.5°	645.4
40°	613.8
42.5°	579.5
45°	537.4
47.5°	497.9
50°	453.1
52.5°	405.7
55°	355.7
57.5°	308.2
60°	263.4
62.5°	218.7
65°	176.6
67.5°	137.0
70°	100.1
72.5°	68.4
75°	39.6
77.5°	18.4
80°	2.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)