

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211433

Luminaire Tested: **LE_4B15D010 EC4B10209050 4LBS1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209050 4LBS1WMH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1504.4 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211433

CATALOG NUMBER: LE_4B15D010 EC4B10209050 4LBS1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P211433

CATALOG NUMBER: LE_4B15D010 EC4B10209050 4LBS1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86
3	96	88	82	76	94	87	81	76	84	79	74		81	77	73		79
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72
5	83	73	65	59	82	72	64	59	70	63	59		68	62	58		66
6	78	66	59	53	76	65	58	53	64	57	53		62	57	52		61
7	73	61	53	48	71	60	53	48	59	52	48		57	52	47		56
8	68	56	49	44	67	56	48	43	54	48	43		53	47	43		52
9	64	52	45	40	63	52	45	40	50	44	40		49	44	39		49
10	60	48	41	37	59	48	41	37	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211433

CATALOG NUMBER: LE_4B15D010 EC4B10209050 4LBS1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.1	5.9
10°-20°	233.5	15.5
20°-30°	313.6	20.8
30°-40°	321.0	21.3
40°-50°	277.9	18.5
50°-60°	184.8	12.3
60°-70°	75.9	5.0
70°-80°	9.0	0.6
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	635.3	42.2
0°-40°	956.4	63.6
0°-60°	1419.1	94.3
0°-90°	1504.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1504.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	954	
5°	939	88
15°	834	234
25°	684	314
35°	513	321
45°	362	278
55°	205	185
65°	75	76
75°	4	9
85°	0	0
90°	0	



TEST NUMBER: P211433

CATALOG NUMBER: LE_4B15D010 EC4B10209050 4LBS1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	953.5
2.5°	951.5
5°	938.8
7.5°	919.1
10°	892.4
12.5°	862.8
15°	834.3
17.5°	797.7
20°	762.2
22.5°	724.8
25°	684.3
27.5°	640.9
30°	597.5
32.5°	554.1
35°	512.7
37.5°	473.3
40°	435.8
42.5°	398.3
45°	361.9
47.5°	323.4
50°	284.0
52.5°	244.5
55°	205.1
57.5°	170.6
60°	135.1
62.5°	102.5
65°	74.9
67.5°	49.3
70°	28.7
72.5°	13.8
75°	3.9
77.5°	2.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)