

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211438

Luminaire Tested: **LE_4B15D010 EC4B10209050 4LBW1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209050 4LBW1MW
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1319.7 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211438

CATALOG NUMBER: LE_4B15D010 EC4B10209050 4LBW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211438

CATALOG NUMBER: LE_4B15D010 EC4B10209050 4LBW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		93
2	103	96	91	86	101	94	89	85	91	87	83		88	84	81		85
3	96	87	80	75	93	85	79	74	83	77	73		80	76	72		78
4	89	79	72	66	87	78	71	66	75	69	65		73	68	64		71
5	83	72	64	59	81	71	64	58	69	63	58		67	62	57		65
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		60
7	73	61	53	48	71	60	53	48	59	52	47		57	51	47		56
8	68	56	49	44	67	56	49	44	54	48	43		53	47	43		52
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	61	49	42	37	59	48	41	37	47	41	37		46	41	37		46

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211438

CATALOG NUMBER: LE_4B15D010 EC4B10209050 4LBW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.1	5.7
10°-20°	210.0	15.9
20°-30°	296.7	22.5
30°-40°	287.4	21.8
40°-50°	193.9	14.7
50°-60°	120.4	9.1
60°-70°	80.5	6.1
70°-80°	44.0	3.3
80°-90°	11.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	581.8	44.1
0°-40°	869.2	65.9
0°-60°	1183.5	89.7
0°-90°	1319.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1319.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	800	
5°	793	75
15°	745	210
25°	651	297
35°	462	287
45°	248	194
55°	132	120
65°	80	80
75°	41	44
85°	10	12
90°	0	



TEST NUMBER: P211438

CATALOG NUMBER: LE_4B15D010 EC4B10209050 4LBW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	799.7
2.5°	799.7
5°	792.9
7.5°	784.3
10°	774.0
12.5°	763.7
15°	744.8
17.5°	729.4
20°	703.8
22.5°	678.1
25°	650.6
27.5°	613.1
30°	571.9
32.5°	518.9
35°	462.4
37.5°	405.8
40°	349.3
42.5°	292.8
45°	248.2
47.5°	207.2
50°	176.3
52.5°	150.7
55°	131.9
57.5°	116.5
60°	104.4
62.5°	92.5
65°	80.5
67.5°	70.2
70°	60.0
72.5°	51.4
75°	41.1
77.5°	32.5
80°	24.0
82.5°	17.2
85°	10.3
87.5°	3.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)