

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211664

Luminaire Tested: **LE_4B20D010 EC4B10208035 4LBS1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211664
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10208035 4LBS1WH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2377.3 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211664

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBS1WH

Luminous Intensity Polar Plot





TEST NUMBER: P211664

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBS1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	111	107	104	101	108	105	102	99		101	98	96			97	95	93			94
2	103	96	90	85	100	94	89	84		91	86	83			87	84	81			85
3	95	86	79	73	93	84	78	73		82	76	72			79	74	70			76
4	88	77	70	64	86	76	69	63		74	68	63			72	66	62			69
5	81	70	62	56	79	69	62	56		67	60	55			65	59	55			63
6	76	64	56	50	74	63	55	50		61	54	49			60	54	49			58
7	71	58	51	45	69	58	50	45		56	49	45			55	49	44			54
8	66	54	46	41	65	53	46	41		52	45	40			51	45	40			50
9	62	50	42	37	61	49	42	37		48	41	37			47	41	37			46
10	58	46	39	34	57	46	39	34		45	38	34			44	38	34			43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211664

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBS1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.8	5.5
10°-20°	338.5	14.2
20°-30°	442.7	18.6
30°-40°	468.8	19.7
40°-50°	437.2	18.4
50°-60°	331.1	13.9
60°-70°	179.4	7.5
70°-80°	48.1	2.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	911.9	38.4
0°-40°	1380.7	58.1
0°-60°	2149.1	90.4
0°-90°	2377.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2377.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1418	
5°	1397	131
15°	1210	338
25°	963	443
35°	749	469
45°	570	437
55°	372	331
65°	180	179
75°	42	48
85°	0	1
90°	0	



TEST NUMBER: P211664

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBS1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1417.8
2.5°	1412.5
5°	1397.0
7.5°	1363.1
10°	1318.9
12.5°	1267.0
15°	1209.6
17.5°	1144.7
20°	1087.4
22.5°	1022.3
25°	962.6
27.5°	902.7
30°	845.5
32.5°	796.0
35°	749.2
37.5°	702.4
40°	658.2
42.5°	614.0
45°	569.7
47.5°	520.3
50°	470.8
52.5°	421.4
55°	372.0
57.5°	319.9
60°	270.5
62.5°	223.8
65°	179.5
67.5°	137.9
70°	101.5
72.5°	70.3
75°	41.6
77.5°	18.2
80°	5.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)