

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211665

Luminaire Tested: **LE_4B20D010 EC4B10208035 4LBS1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211665
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10208035 4LBS1WMH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2397.0 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211665

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBS1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P211665

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBS1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	102		109	106	103	101		102	100	97		98	96	94		95	93	92
2	104	98	92	88		102	96	91	87		92	88	85		89	86	83		86	84	81
3	96	88	82	76		94	87	81	76		84	79	74		81	77	73		79	75	72
4	90	80	73	67		88	79	72	67		76	70	66		74	69	65		72	68	64
5	83	73	65	59		82	72	64	59		70	63	59		68	62	58		66	61	57
6	78	66	59	53		76	65	58	53		64	57	53		62	57	52		61	56	52
7	73	61	53	48		71	60	53	48		59	52	48		57	52	47		56	51	47
8	68	56	49	44		67	56	48	43		54	48	43		53	47	43		52	47	43
9	64	52	45	40		63	52	45	40		50	44	40		49	44	39		49	43	39
10	60	48	41	37		59	48	41	37		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211665

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBS1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	5.9
10°-20°	372.1	15.5
20°-30°	499.7	20.8
30°-40°	511.5	21.3
40°-50°	442.8	18.5
50°-60°	294.5	12.3
60°-70°	120.9	5.0
70°-80°	14.4	0.6
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1012.2	42.2
0°-40°	1523.8	63.6
0°-60°	2261.1	94.3
0°-90°	2397.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2397.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1519	
5°	1496	140
15°	1329	372
25°	1090	500
35°	817	512
45°	577	443
55°	327	294
65°	119	121
75°	6	14
85°	0	1
90°	0	



TEST NUMBER: P211665

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBS1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1519.3
2.5°	1516.1
5°	1495.7
7.5°	1464.3
10°	1421.8
12.5°	1374.7
15°	1329.1
17.5°	1271.0
20°	1214.4
22.5°	1154.8
25°	1090.3
27.5°	1021.1
30°	952.0
32.5°	883.0
35°	817.0
37.5°	754.1
40°	694.4
42.5°	634.8
45°	576.6
47.5°	515.3
50°	452.5
52.5°	389.6
55°	326.8
57.5°	271.8
60°	215.2
62.5°	163.4
65°	119.4
67.5°	78.5
70°	45.6
72.5°	22.0
75°	6.3
77.5°	3.1
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)