

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211467

Luminaire Tested: **LE_4B20D010 EC4B10209024 4LBW1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211467
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209024 4LBW1MW
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1482.2 lumens
Efficiency: N/A
Efficacy: 71.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211467

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211467

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88						
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78						
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69						
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61						
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55						
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50						
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45						
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41						
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38						
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35						

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211467

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.3	5.7
10°-20°	235.8	15.9
20°-30°	333.3	22.5
30°-40°	322.9	21.8
40°-50°	217.8	14.7
50°-60°	135.2	9.1
60°-70°	90.4	6.1
70°-80°	49.4	3.3
80°-90°	13.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	653.5	44.1
0°-40°	976.4	65.9
0°-60°	1329.4	89.7
0°-90°	1482.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1482.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	898	
5°	890	84
15°	837	236
25°	731	333
35°	519	323
45°	279	218
55°	148	135
65°	90	90
75°	46	49
85°	12	13
90°	0	



TEST NUMBER: P211467

CATALOG NUMBER: LE_4B20D010 EC4B10209024 4LBW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	898.2
2.5°	898.2
5°	890.5
7.5°	880.9
10°	869.4
12.5°	857.8
15°	836.7
17.5°	819.4
20°	790.5
22.5°	761.7
25°	730.9
27.5°	688.6
30°	642.4
32.5°	582.8
35°	519.3
37.5°	455.9
40°	392.4
42.5°	328.9
45°	278.9
47.5°	232.7
50°	198.1
52.5°	169.2
55°	148.1
57.5°	130.8
60°	117.3
62.5°	103.8
65°	90.4
67.5°	78.9
70°	67.3
72.5°	57.7
75°	46.2
77.5°	36.5
80°	26.9
82.5°	19.3
85°	11.5
87.5°	3.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)