

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211681

Luminaire Tested: **LE_4B20D010 EC4B10209035 4LBN1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211681
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209035 4LBN1B
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 789.5 lumens
Efficiency: N/A
Efficacy: 38.0 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211681

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBN1B

Luminous Intensity Polar Plot





TEST NUMBER: P211681

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBN1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	107	111	109	107	105		105	103	102		101	100	99		98	97	96
2	109	104	100	97	106	102	99	96		99	96	94		96	94	92		93	92	90
3	104	98	93	89	102	96	92	88		94	90	87		91	88	86		89	86	84
4	99	92	86	82	97	90	86	82		88	84	81		86	83	80		85	82	79
5	94	86	81	77	92	85	80	76		84	79	76		82	78	75		80	77	74
6	90	81	76	72	88	81	75	71		79	74	71		78	74	70		76	73	70
7	86	77	71	67	84	76	71	67		75	70	67		74	69	66		73	69	66
8	82	73	67	63	80	72	67	63		71	66	63		70	66	62		69	65	62
9	78	69	63	60	77	68	63	59		67	63	59		67	62	59		66	62	59
10	75	65	60	56	74	65	60	56		64	59	56		63	59	56		63	59	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211681

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBN1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.6	13.6
10°-20°	228.1	28.9
20°-30°	264.7	33.5
30°-40°	165.7	21.0
40°-50°	23.3	3.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	600.4	76.1
0°-40°	766.1	97.0
0°-60°	789.5	100.0
0°-90°	789.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	789.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1291	
5°	1196	108
15°	811	228
25°	584	265
35°	266	166
45°	21	23
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211681

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBN1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1290.8
2.5°	1265.4
5°	1196.2
7.5°	1096.9
10°	995.3
12.5°	898.3
15°	810.6
17.5°	736.7
20°	681.3
22.5°	630.5
25°	584.3
27.5°	528.8
30°	457.3
32.5°	367.1
35°	265.5
37.5°	173.2
40°	99.3
42.5°	50.8
45°	20.8
47.5°	4.6
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)