

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211656

Luminaire Tested: **LE_4B20D010 EC4B10208035 4LBN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211656
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10208035 4LBN1MW
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1717.6 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211656

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBN1MW

Luminous Intensity Polar Plot






TEST NUMBER: P211656

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	80	96	89	83	79	86	82	78		84	80	76		81
4	92	83	76	71	90	82	76	71	80	74	70		78	73	69		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62
8	73	62	55	50	71	61	55	50	60	54	50		59	53	49		58
9	69	58	51	46	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	43	64	54	47	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211656

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.8	7.8
10°-20°	352.7	20.5
20°-30°	464.2	27.0
30°-40°	361.3	21.0
40°-50°	175.5	10.2
50°-60°	110.9	6.5
60°-70°	71.6	4.2
70°-80°	37.4	2.2
80°-90°	9.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	951.6	55.4
0°-40°	1312.9	76.4
0°-60°	1599.3	93.1
0°-90°	1717.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1717.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1465	
5°	1438	135
15°	1258	353
25°	1023	464
35°	578	361
45°	218	176
55°	123	111
65°	71	72
75°	36	37
85°	8	9
90°	0	



TEST NUMBER: P211656

CATALOG NUMBER: LE_4B20D010 EC4B10208035 4LBN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1465.2
2.5°	1457.0
5°	1437.8
7.5°	1405.1
10°	1361.5
12.5°	1312.3
15°	1257.8
17.5°	1200.5
20°	1140.5
22.5°	1083.2
25°	1023.1
27.5°	946.8
30°	843.1
32.5°	720.2
35°	578.4
37.5°	447.4
40°	346.5
42.5°	270.2
45°	218.3
47.5°	177.4
50°	155.6
52.5°	139.2
55°	122.7
57.5°	109.2
60°	95.5
62.5°	81.9
65°	71.0
67.5°	62.8
70°	51.9
72.5°	43.6
75°	35.5
77.5°	27.3
80°	19.1
82.5°	13.7
85°	8.2
87.5°	2.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)