

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211689

Luminaire Tested: **LE_4B20D010 EC4B10209035 4LBS1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211689
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209035 4LBS1GPH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1833.9 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211689

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBS1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P211689

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBS1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	105	102	99	101	98	96		97	95	93		93
2	102	95	89	84	100	93	88	83	90	85	82		87	83	80		84
3	94	85	78	72	92	83	77	71	80	75	70		78	73	69		75
4	87	76	68	62	85	75	67	62	72	66	61		70	65	60		68
5	80	68	60	54	78	67	60	54	65	59	53		63	58	53		62
6	74	62	54	48	73	61	53	48	59	52	47		58	52	47		56
7	69	57	48	43	68	56	48	43	54	47	42		53	47	42		52
8	65	52	44	38	63	51	44	38	50	43	38		49	42	38		48
9	60	48	40	35	59	47	40	35	46	39	35		45	39	34		44
10	57	44	37	32	56	44	36	32	43	36	31		42	36	31		41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211689

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBS1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.2	4.4
10°-20°	225.1	12.3
20°-30°	328.3	17.9
30°-40°	374.4	20.4
40°-50°	359.1	19.6
50°-60°	275.1	15.0
60°-70°	150.9	8.2
70°-80°	40.1	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	633.6	34.6
0°-40°	1008.0	55.0
0°-60°	1642.2	89.5
0°-90°	1833.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1833.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	852	
5°	845	80
15°	799	225
25°	713	328
35°	599	374
45°	467	359
55°	308	275
65°	152	151
75°	35	40
85°	0	1
90°	0	



TEST NUMBER: P211689

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBS1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	851.8
2.5°	849.6
5°	845.2
7.5°	838.6
10°	829.7
12.5°	814.3
15°	798.9
17.5°	781.3
20°	761.5
22.5°	737.3
25°	713.1
27.5°	688.9
30°	658.1
32.5°	629.4
35°	598.7
37.5°	567.8
40°	537.0
42.5°	504.0
45°	466.6
47.5°	429.2
50°	389.5
52.5°	347.8
55°	308.1
57.5°	268.5
60°	226.7
62.5°	187.1
65°	151.8
67.5°	116.7
70°	85.8
72.5°	57.2
75°	35.3
77.5°	15.4
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)