

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211693

Luminaire Tested: **LE_4B20D010 EC4B10209035 4LBS1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209035 4LBS1WH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2009.8 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211693

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBS1WH

Luminous Intensity Polar Plot






TEST NUMBER: P211693

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBS1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	96	90	85	100	94	89	84	91	86	83		87	84	81		85
3	95	86	79	73	93	84	78	73	82	76	72		79	74	70		76
4	88	77	70	64	86	76	69	63	74	68	63		72	66	62		69
5	81	70	62	56	79	69	62	56	67	60	55		65	59	55		63
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58
7	71	58	51	45	69	58	50	45	56	49	45		55	49	44		54
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211693

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBS1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.5	5.5
10°-20°	286.1	14.2
20°-30°	374.3	18.6
30°-40°	396.3	19.7
40°-50°	369.6	18.4
50°-60°	279.9	13.9
60°-70°	151.6	7.5
70°-80°	40.7	2.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	771.0	38.4
0°-40°	1167.3	58.1
0°-60°	1816.9	90.4
0°-90°	2009.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2009.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1199	
5°	1181	111
15°	1023	286
25°	814	374
35°	633	396
45°	482	370
55°	314	280
65°	152	152
75°	35	41
85°	0	1
90°	0	



TEST NUMBER: P211693

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBS1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1198.6
2.5°	1194.2
5°	1181.0
7.5°	1152.5
10°	1115.0
12.5°	1071.0
15°	1022.7
17.5°	967.7
20°	919.3
22.5°	864.3
25°	813.7
27.5°	763.2
30°	714.8
32.5°	673.0
35°	633.4
37.5°	593.8
40°	556.5
42.5°	519.0
45°	481.6
47.5°	439.9
50°	398.1
52.5°	356.2
55°	314.5
57.5°	270.5
60°	228.8
62.5°	189.2
65°	151.7
67.5°	116.6
70°	85.7
72.5°	59.4
75°	35.1
77.5°	15.4
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)